

DisplayPort to HDMI Adapter Video Converter (M/F), 50 Pack

MODEL NUMBER: P136-000-1-BP



Passive adapter connects your DisplayPort (DP) computer to an HDMI television, monitor or projector for playing audio and 1080p video.

Features

A Smart Solution for Displaying 1080p Video in Business and Digital Signage Applications This set includes 50 P136-000-1 DisplayPort-to-HDMI passive adapters (M/F). Each adapter allows you to play stereo audio and high-definition video from your DisplayPort computer or laptop to an HDMI television, monitor or projector. This allows you to continue using your existing HDMI display without the time, effort or expense of replacing it with a new DP monitor. These adapters are an easy, inexpensive way to play 1080p video in classrooms, conference rooms, trade shows and other on-the-road presentations.

Ready to Use Right Out of the Package Ideal for displaying video on a large monitor or digital sign, each fully molded adapter measures just over two inches in length, making it perfect for carrying in your pocket, briefcase, purse or laptop bag for convenient use anywhere. Just connect the male DP end to your computer's DisplayPort and the female HDMI end to an HDMI cable to begin sharing HD audio/video signals. The plug-and-play adapter requires no software, drivers or external power.

Enjoy Outstanding 1080p Picture Quality on Any HDMI Display Each P136-000-1 adapter supports video resolutions up to 1920 x 1200, HD resolutions up to 1080p, and DTS-HD, Dolby TrueHD and 7.1-channel surround sound audio.

Passive Adapters Require DisplayPort++ for HDMI Pass Through Because they are passive adapters, these units require that the connected source device have a DisplayPort++ (DP++) dual-mode port, which allows HDMI signals to pass through. Check your DisplayPort source's documentation for compatibility.

Highlights

- 50-piece bulk pack of P136-000-1 DisplayPort to HDMI adapter converters
- Delivers hi-def picture quality at resolutions up to 1920 x 1200 (1080p)
- Supports DTS-HD, Dolby TrueHD and 7.1-channel surround sound audio
- Compact unit fits easily into pocket, briefcase or laptop bag for use anywhere
- Plug-and-play operation with no software required for easy, immediate installation

Applications

- Play video from your DP laptop or PC on an HDMI display device, such as an HDTV
- Access documents and websites across multiple displays
- Design and edit graphics files or production video on a larger HDMI monitor
- Using a DisplayPort laptop to deliver presentations in a classroom or conference room
- Display menus, ads, promos, directions and other digital signage applications on an HD monitor

System Requirements

- Source device with DisplayPort output and DP++ port for HDMI pass-through (must support audio to transmit audio signals)
- Display device with HDMI input

Package Includes

- (50) P136-000-1 DisplayPort to HDMI Video Adapter Converters, M/F

Specifications

OVERVIEW	
UPC Code	037332237651
Product Type	Video Adapter



Powering Business Worldwide



Technology	HDMI; DisplayPort
VIDEO	
Max Supported Video Resolution	1920 x 1200 (1080p)
Max Supported Color Depth	36-bit Deep Color
INPUT	
Product Length (in.)	2.31
Product Length (ft.)	0.19
CONNECTIONS	
Side A - Connector 1	DISPLAYPORT (MALE)
Side B - Connector 1	HDMI (FEMALE)
Connector Plating	Gold
Contact Plating	Gold
PHYSICAL	
Color	Black
Material of Construction	PCB
Shipping Dimensions (hwd / in.)	1.00 x 13.50 x 15.75
Shipping Weight (kg)	0.86
Unit Dimensions (hwd / in.)	2.310 x 0.550 x 0.890
Unit Weight (lbs.)	0.09
Unit Weight (kg)	0.04
ENVIRONMENTAL	
Operating Temperature Range	32° to 113°F (0° to 45°C)
Storage Temperature Range	14° to 176°F (-10° to 80°C)
Operating Humidity Range	10% to 85% RH, Non-Condensing
Storage Humidity Range	5% to 90% RH, Non-Condensing
FEATURES & SPECIFICATIONS	
Displayport Specification	1.1a
HDCP Specification	1.3
Driver Required	No
STANDARDS & COMPLIANCE	
Product Compliance	CE (Europe); FCC (USA); REACH; RoHS; UKCA; WEEE



Powering Business Worldwide



WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.