

DisplayPort to VGA/DVI/HDMI All-in-One Converter Adapter, DP ver 1.2, 4K 30 Hz HDMI

MODEL NUMBER: P136-06N-HDV-4K



All-in-one converter/adapter connects your DisplayPort-enabled laptop or tablet to a VGA, DVI or HDMI display without the need to carry separate adapters. Ideal for trade shows, classrooms and lecture halls.

Description

No more carrying around separate adapters for various monitors, projectors and televisions. The P136-06N-HDV-4K DisplayPort 1.2 to VGA/DVI/HDMI All-in-One Converter Adapter connects your laptop or tablet's DisplayPort to a VGA, DVI or HDMI display. The simple all-in-one solution for displaying content on a larger screen, the P136-06N-HDV-4K is ideal for trade shows, classrooms, lecture halls and other presentations.

The all-in-one unit contains separate female DVI, HD15 and HDMI ports. It supports video resolutions up to 1920 x 1080 (DVI); 1920 x 1200, including 1080p (HD15); and 3840 x 2160 (HDMI). It also supports 36-bit Deep Color (12 bits per channel). The passive adapter requires the connected computer to have a DP++ (DisplayPort++) port.

The P136-06N-HDV-4K is compatible with laptops, tablets and other devices equipped with a female DisplayPort. It's completely plug-and-play with no software, drivers or external power supply needed. With its small size and built-in cable, the P136-06N-HDV-4K is perfect for stowing in your laptop bag and carrying to school, the office or the latest trade show.

Features

Connects Your DisplayPort Laptop or Tablet to a VGA, DVI or HDMI Display

- Recommended for trade shows, classrooms, lecture halls and other presentations
- DVI port supports video resolutions up to 1920 x 1080 (1080p)
- HD15 port supports video resolutions up to 1920 x 1200, including 1080p
- HDMI port supports UHD video resolutions up to 3840 x 2160 (4K x 2K) @ 24/30 Hz
- Supports 36-bit Deep Color (12 bits per channel)

Highlights

- Separate DVI, HD15 and HDMI female connectors
- HDMI port supports UHD 4K x 2K @ 24/30 Hz video resolutions
- Passive adapter requires connected computer to have DP++ port
- Plug and play—no software, drivers or power supply needed
- Small size for easy carrying in laptop bag or briefcase

System Requirements

- The P136-06N-HDV-4K is a Passive adapter, and requires the connected computer to have a DP++ (Displayport ++) port

Package Includes

- P136-06N-HDV-4K DisplayPort 1.2 to VGA/DVI/HDMI All-in-One Converter Adapter, 6 in.
- Owner's manual



- 7.1 Audio Surround Sound only supported by HDMI

Plug-and-Play Convenience

- No software, drivers or external power supply required
- Small enough to stow in laptop bag or briefcase
- Passive adapter requires connected computer to have DP++ port

Specifications

OVERVIEW	
UPC Code	037332190840
Technology	DVI; HDMI; VGA/SVGA; DisplayPort
PHYSICAL	
Color	Black
Shipping Dimensions (hwd / cm)	10.01 x 14.00 x 2.31
Shipping Dimensions (hwd / in.)	3.94 x 5.51 x 0.91
Shipping Weight (kg)	0.07
Shipping Weight (lbs.)	0.16
CONNECTIONS	
Side A - Connector 1	DISPLAYPORT (MALE)
Side B - Connector 1	DVI-D DUAL-LINK (FEMALE) (WIRED TO DVI-D SINGLE-LINK)
Side B - Connector 2	HD15 (FEMALE)
Side B - Connector 3	HDMI (FEMALE)
WARRANTY	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>