

DisplayPort to VGA/DVI/HDMI All-in-One Converter Adapter - 4K 60 Hz HDMI, DP 1.2

MODEL NUMBER: P136-06N-HDV4K6



All-in-one converter/adapter connects your DisplayPort-enabled laptop or tablet to a VGA, DVI or HDMI display without the need to carry separate adapters.

Description

No more carrying around separate adapters for various monitors, projectors and televisions. The P136-06N-HDV4K6 DisplayPort 1.2 to VGA/DVI/HDMI All-in-One Converter Adapter connects your laptop or tablet's DisplayPort to a VGA, DVI or HDMI display. The simple all-in-one solution for displaying content on a larger screen, the P136-06N-HDV4K6 is ideal for trade shows, classrooms, lecture halls and anywhere else you might give a presentation.

The all-in-one unit contains separate female DVI, HD15 and HDMI ports. It supports video resolutions up to 1920 x 1080, including 1080p (DVI); 1920 x 1200, including 1080p (HD15); and 4K x 2K (HDMI) at 60 Hz, as specified in HDMI 2.0. It also supports 36-bit Deep Color (12 bits per channel). This adapter supports HDCP 2.2.

The P136-06N-HDV4K6 is compatible with laptops, tablets and other devices equipped with a female DisplayPort. It's completely plug-and-play with no software, drivers or external power supply needed. With its small size and built-in cable, the P136-06N-HDV4K6 is recommended for stowing in your laptop bag and carrying to school, the office or the latest trade show.

Features

Connects Your DisplayPort Laptop or Tablet to a VGA, DVI or HDMI Display Recommended for trade shows, classrooms, lecture halls and other presentation venues
 DVI port supports video resolutions up to 1920 x 1080 (1080p)
 HD15 port supports video resolutions up to 1920 x 1200, including 1080p
 HDMI port supports video resolutions up to 4K x 2K (3840 x 2160) @ 60 Hz, as specified in HDMI 2.0
 Supports 36-bit Deep Color (12 bits per channel)
 Supports HDCP 2.2

Plug-and-Play Convenience No software, drivers or external power supply required
 Small enough to stow in laptop bag or briefcase

Specifications

OVERVIEW	
UPC Code	037332202741
Product Type	Video Adapter

Highlights

- Separate DVI, HD15 and HDMI female connectors
- Supports UHD resolutions up to 4K @ 60 Hz for crystal-clear video
- Supports HDCP 2.2
- Plug-and-play operation with no software required for easy, immediate installation
- Small size for easy carrying in laptop bag or briefcase

System Requirements

- Computer or tablet with DisplayPort output
- Display device with VGA, DVI or HDMI input

Package Includes

- P136-06N-HDV4K6 DisplayPort 1.2 to VGA/DVI/HDMI All-in-One Converter Adapter, 6 in.
- Owner's manual



Powering Business Worldwide

TRIPP LITE
SERIES

Technology	DVI; HDMI; VGA/SVGA; DisplayPort
CONNECTIONS	
Side A - Connector 1	DISPLAYPORT (MALE)
Side B - Connector 1	DVI-D SINGLE LINK (FEMALE)
Side B - Connector 2	HD15 (FEMALE)
Side B - Connector 3	HDMI (FEMALE)
PHYSICAL	
Color	Black
Cable Length (in.)	6
Shipping Dimensions (hwd / in.)	0.90 x 3.90 x 5.60
Shipping Dimensions (hwd / cm)	2.29 x 9.91 x 14.22
Shipping Weight (lbs.)	0.20
Shipping Weight (kg)	0.09
FEATURES & SPECIFICATIONS	
HDCP Specification	2.2
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.