

Keyspan Mini DisplayPort 1.2 to Active VGA Adapter, Video Converter for Mac/PC, Thunderbolt 1 & 2 Compatible, 1920x1200 1080p (M/F)

MODEL NUMBER: P137-000-VGA



Connect a VGA monitor to a Mac or PC with a Mini Displayport output

Description

The P137-000-VGA Mini-DisplayPort 1.2 to VGA Adapter allows you to connect a Mac or PC with a Mini-DisplayPort or Thunderbolt output to a VGA monitor. Ideal for Thunderbolt/Mini DisplayPort equipped laptops, Chromebooks, MacBooks and Microsoft Surface. Mac (up to OSX 10.12) and Windows (up to 10) Compatible.

Supports computer video resolutions up to 1920 x 1200 and HD resolutions up to 1080p. Fully-molded compact one-piece design ensures long life enjoyment.

Features a simple plug-and-play design with an integrated chip that converts the digital Mini-DisplayPort signal to analog VGA; no drivers or setup needed. Simply plug the adapter into your Mini-DisplayPort /Thunderbolt source and connect your VGA cable between it and your monitor.

Unlike passive adapters, active adapters convert both Single-Mode and Dual-Mode (DP++) DisplayPort output. Ideal for use with graphics cards, such as AMD Eyefinity, that do not output Dual Mode (DP++) signals.

Features

- Compact 1-piece design
- Connect a VGA monitor to a Mac or PC/Windows with a Mini DisplayPort or Thunderbolt 1/2 output
- Displayport 1.2 compliant
- Plug-and-play convenience—no drivers or software needed
- Supports computer video resolutions up to 1920 x 1200, and HD resolutions up to 1080p
- Ideal for use with graphics cards, such as AMD Eyefinity, that do not output Dual Mode (DP++) signals
- Converts both Single-Mode and Dual Mode (DP++) Displayport output

Highlights

- Compact 1-piece design
- Connect a VGA monitor to a Mac or PC/Windows with a Mini DisplayPort or Thunderbolt 1/2 output
- Supports computer video resolutions up to 1920 x 1200, and HD resolutions up to 1080p
- Ideal for use with graphics cards, such as AMD Eyefinity, that do not output Dual Mode (DP++) signals
- Converts both Single-Mode and Dual Mode (DP++) Displayport output

System Requirements

- Mac (up to OSX 10.12) or PC/Windows (up to 10) with a Mini Displayport port; Compatible with Thunderbolt 1 and 2 ports on Mac computers
- Monitor with a VGA port

Package Includes

- Mini-Displayport 1.2 to Active VGA Adapter

Specifications

OVERVIEW	
UPC Code	037332184825



Powering Business Worldwide

TRIPP LITE
SERIES

Product Type	Video Adapter
Technology	VGA/SVGA; DisplayPort
CONNECTIONS	
Side A - Connector 1	MINI DISPLAYPORT (MALE)
Side B - Connector 1	HD15 (FEMALE)
PHYSICAL	
Color	Black
Shipping Dimensions (hwd / in.)	1.80 x 3.60 x 5.40
Shipping Dimensions (hwd / cm)	4.57 x 9.14 x 13.72
Shipping Weight (lbs.)	0.20
Shipping Weight (kg)	0.09
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.