

Keyspan Mini DisplayPort to DVI Adapter, Video Converter for Mac/PC, White (M/F), 6-in. (15.24 cm)

MODEL NUMBER: **P137-06N-DVI**



Features

- Convert your Mac or PC's Mini Displayport signal for use with your DVI display
- Compatible with Thunderbolt 1 and 2 ports on Mac computers
- Mini Displayport Male to DVI-I Female; fully molded ends
- Supports DVI Single Link computer video resolutions up to 1920 x 1200, and HD resolutions up to 1080p
- The P137-06N-DVI is a Passive adapter, and requires that the connected computer has a DP++ (Displayport ++) port, which allows HDMI and DVI signals to be passed through; check the documentation for your Mini Displayport source for compatibility.

Highlights

- Connect a DVI monitor to a Mac or PC with a Mini Displayport output
- Compatible with Thunderbolt 1 and 2 ports on Mac computers
- Plug-and-play convenience—no drivers or software needed
- Supports DVI Single Link computer video resolutions up to 1920 x 1200, and HD resolutions up to 1080p
- This product is a passive adapter and requires that the connected computer has a DP++ (DisplayPort ++) dual-mode port

System Requirements

- A Mac or PC with a Mini Displayport port; Compatible with Thunderbolt 1 and 2 ports on Mac computers
- A monitor with a DVI port
- The P137-06N-DVI is a Passive adapter, and requires that the connected computer has a DP++ (DisplayPort ++) port, which allows HDMI and DVI signals to be passed through; check the documentation for your Mini Displayport source for compatibility.
- Not for use with MST Hubs. For compatibility with MST Hubs, use a Displayport 1.2 compliant product such as P137-06N-DVI-V2

Package Includes

- P137-06N-DVI Mini Displayport to DVI Adapter

Specifications

OVERVIEW	
UPC Code	037332158888
Product Type	Video Adapter
Technology	DVI; DisplayPort
CONNECTIONS	
Side A - Connector 1	MINI DISPLAYPORT (MALE)



Powering Business Worldwide



Side B - Connector 1	DVI-I (FEMALE)
PHYSICAL	
Color	White
Cable Length (ft.)	0.5
Cable Length (m)	0.15
Cable Length (in.)	6
Cable Length (cm)	15.24
Shipping Dimensions (hwd / in.)	0.50 x 7.00 x 9.00
Shipping Dimensions (hwd / cm)	1.27 x 17.78 x 22.86
Shipping Weight (lbs.)	0.11
Shipping Weight (kg)	0.05
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; Trade Agreements Act (TAA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.