

## Keyspan Mini DisplayPort to DVI Adapter, Video Converter for Mac/PC, White (M/F), 6 in.

MODEL NUMBER: **P137-06N-DVI**



### Description

Tripp Lite's P137-06N-DVI, Mini DisplayPort Male to DVI Female adapter allows you to connect a Mac or PC with a Mini DisplayPort or Thunderbolt™ output to a DVI monitor. Ideal for Thunderbolt™ /Mini DisplayPort equipped laptops, Chromebooks, Ultrabooks, MacBooks, and Microsoft Surface. Also Mac 10.11, Windows 10 Compatible.

Supports DVI Single Link computer video resolutions up to 1920 x 1200, and HD resolutions up to 1080p. Fully molded ends ensure long life enjoyment.

The P137-06N-DVI is a Passive adapter, and requires that the connected computer has a DP++ ( DisplayPort ++ ) port, which allows HDMI and DVI signals to be passed through; check the documentation for your Mini DisplayPort source for compatibility.

### Features

- Convert your Mac or PC's Mini Displayport signal for use with your DVI display
- Compatible with Thunderbolt 1 and 2 ports on Mac computers
- Mini Displayport Male to DVI-I Female; fully molded ends
- Supports DVI Single Link computer video resolutions up to 1920 x 1200, and HD resolutions up to 1080p
- The P137-06N-DVI is a Passive adapter, and requires that the connected computer has a DP++ ( Displayport ++ ) port, which allows HDMI and DVI signals to be passed through; check the documentation for your Mini Displayport source for compatibility.

### Highlights

- Connect a DVI monitor to a Mac or PC with a Mini Displayport output
- Compatible with Thunderbolt 1 and 2 ports on Mac computers
- Plug-and-play convenience—no drivers or software needed
- Supports DVI Single Link computer video resolutions up to 1920 x 1200, and HD resolutions up to 1080p
- This product is a passive adapter and requires that the connected computer has a DP++ (DisplayPort ++ ) dual-mode port

### System Requirements

- A Mac or PC with a Mini Displayport port; Compatible with Thunderbolt 1 and 2 ports on Mac computers
- A monitor with a DVI port
- The P137-06N-DVI is a Passive adapter, and requires that the connected computer has a DP++ ( DisplayPort ++ ) port, which allows HDMI and DVI signals to be passed through; check the documentation for your Mini Displayport source for compatibility.
- Not for use with MST Hubs. For compatibility with MST Hubs, use a Displayport 1.2 compliant product such as P137-06N-DVI-V2



#### Package Includes

- Keyspan by Tripp Lite P137-06N-DVI Mini Displayport to DVI Adapter

## Specifications

OVERVIEW	
UPC Code	037332158888
INPUT	
Cable Length (ft.)	0.5
Cable Length (m)	0.2
Cable Length (in.)	6
Cable Length (cm)	15.24
PHYSICAL	
Color	White
Shipping Dimensions (hwd / cm)	1.27 x 17.78 x 22.86
Shipping Dimensions (hwd / in.)	0.50 x 7.00 x 9.00
Shipping Weight (kg)	0.05
Shipping Weight (lbs.)	0.11
CONNECTIONS	
Side A - Connector 1	MINI DISPLAYPORT (MALE)
Side B - Connector 1	DVI-I (FEMALE)
FEATURES & SPECIFICATIONS	
Technology	DVI; DisplayPort
STANDARDS & COMPLIANCE	
Certifications	RoHS
WARRANTY	
Product Warranty Period (Worldwide)	3-year limited warranty



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>