

Connection Requirement

Passive adapter requires connected source device to have a DP++ port that allows HDMI and DVI signals to be passed through. Check your device's manual for compatibility. Not for use with MST hubs. For MST hub compatibility, use a DisplayPort 1.2 compliant unit, such as P137-06N-DVI-V2.

Keyspan Mini DisplayPort to DVI Adapter, Video Converter for Mac/PC, Black (M/F), 6-in. (15.24 cm)

MODEL NUMBER: P137-06N-DVIB



mDP to DVI adapter connects a DVI monitor to the Mini DisplayPort port on your laptop, MacBook, Chromebook or Surface.

Features

More Convenient, Less Expensive Way to Watch 1080p Video This Keyspan® Mini DisplayPort to DVI cable connects the Mini DisplayPort, Thunderbolt 1 or Thunderbolt 2 port on your laptop, MacBook, Chromebook, Ultrabook, notebook or Microsoft Surface to a DVI monitor, projector or television. It features a male mDP connector and a female DVI connector, allowing you to use your existing DVI display and DVI cable to transmit video signals without the expense of buying a new mDP display.

Outstanding 1080p Picture Quality Ideal for digital signage or displaying video in a conference room, lecture hall or home theater, this mDP to DVI cable supports DVI single-link computer video resolutions up to 1920 x 1200, and high-definition resolutions up to 1080p.

Passive Adapter Requires DisplayPort++ Because the P137-06N-DVIB is a passive adapter, the connected laptop, tablet or computer must have a DP++ port. This allows HDMI and DVI signals to be passed through. Check your source device's manual for compatibility.

Ready to Use Right Out of the Package The plug-and-play mDP to DVI cable requires no software, drivers or external power and works with both Windows and Mac operating systems. The six-inch cable fits easily into a briefcase or laptop bag for connecting on the go.

3-Year Warranty and Environmentally Responsible Design The P137-06N-DVIB comes with a 3-year warranty. It's manufactured in compliance with strict RoHS specifications.

Specifications

Highlights

- Keep using your current DVI display with a Mini DisplayPort source
- Delivers high-definition picture quality up to 1920 x 1200, including 1080p
- Compact unit fits easily into briefcase or laptop bag for immediate use anywhere
- Easy installation with plug-and-play operation—no software required
- Ideal for digital signage, video presentations and watching movies in HD

Applications

- Play video or look at photos from your mDP laptop on an HD DVI monitor
- Access documents and websites across multiple displays
- Design and edit graphics files or production video on a larger DVI monitor
- Display menus, ads, promos, directions and other digital signage applications on an HD monitor
- Using your new mDP computer with an existing DVI monitor without an expensive display upgrade

System Requirements

- Source device with Mini DisplayPort, Thunderbolt 1 or Thunderbolt 2 output
- Display device with DVI input
- Source must have DP++, so HDMI and DVI signals may be passed through
- Not for use with MST hubs

Package Includes

- P137-06N-DVIB Keyspan Mini DisplayPort to DVI Adapter, 1080p, 6 in. - M/F, Thunderbolt 1 & 2, Black



Powering Business Worldwide



OVERVIEW	
UPC Code	037332210609
Product Type	Video Adapter
Device Compatibility	Monitor/HDTV
Technology	DVI; DisplayPort
VIDEO	
Supported Resolutions	1920x1200
CONNECTIONS	
Side A - Connector 1	MINI DISPLAYPORT (MALE)
Side B - Connector 1	DVI-I (FEMALE)
Connector Plating	Nickel
Contact Plating	Gold
PHYSICAL	
Color	Black
Cable Length (ft.)	1
Cable Length (m)	0.30
Cable Length (in.)	6
Cable Length (cm)	15
Unit Dimensions (hwd / in.)	0.591 x 1.575 x 7.764
Unit Dimensions (hwd / cm)	1.5 x 4.4 x 4.48
Unit Weight (lbs.)	0
Unit Weight (kg)	0.00
ENVIRONMENTAL	
Operating Temperature Range	32° to 104°F (0° to 40°C)
Storage Temperature Range	-4° to 140°F (-20° to 60°C)
FEATURES & SPECIFICATIONS	
Displayport Specification	1.2
STANDARDS & COMPLIANCE	
Product Certifications	UL Listed; cUL Listed
Product Compliance	CE (Europe); FCC (USA); REACH; RoHS; UKCA; WEEE; Trade Agreements Act (TAA)
WARRANTY & SUPPORT	



Powering Business Worldwide



Product Warranty Period (Worldwide)	3-year limited warranty
--	-------------------------

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.