Keyspan Mini DisplayPort to HDMI Active Adapter/Video Converter (M/F) - 4K 60 Hz, DP 1.2, HDCP 2.2, White, 6 in.

MODEL NUMBER: **P137-06N-H2V2**

Converts Mini DisplayPort (mDP) 1.2 audio and 4K x 2K video for display on an HDMI monitor, projector or television.

Features

Sends Mini DisplayPort 1.2 Audio/Video to an HDMI Display Connects PC or Mac's mDP or Thunderbolt 1 & 2 output to HDMI-enabled monitor, projector or TVIdeal for displaying video on large monitor or digital sign

Vibrant Video Quality Supports UHD video resolutions up to 4K @ 60 Hz (3840 x 2160) as specified in HDMI 2.0Supports audio and HDCP 2.2Converts both Single-Mode and Dual-Mode DisplayPort outputWorks with graphics cards that don't output DP++ signals

Superior Materials for Superior Performance Nickel-plated connectors and gold-plated contacts for excellent conductivityIntegral strain relief for long lifePlug-and-play—no software, drivers or power supply necessaryFits easily into briefcase, backpack or laptop bag

Highlights

- Complies with mDP and Thunderbolt 1 & 2 ports on PCs and Macs
- Supports UHD resolutions up to 4K @ 60 Hz for crystal-clear video
- Supports audio and HDCP 2.2
- Converts both Single-Mode and Dual-Mode mDP output

System Requirements

- PC or Mac with mDP or Thunderbolt 1 & 2 output
- Display with HDMI input
- Both display and source must support 4K x 2K @ 60 Hz to display 4K x 2K video
- Audio supported as long as source does. Check source manual for compatibility.

Package Includes

- P137-06N-H2V2 Keyspan Mini DisplayPort 1.2 to HDMI Active Adapter (M/F), 6 in.

Specifications

OVERVIEW	
UPC Code	037332200341
Product Type	Video Adapter
Technology	HDMI; DisplayPort
CONNECTIONS	
Side A - Connector 1	MINI DISPLAYPORT (MALE)
Side B - Connector 1	HDMI (FEMALE)
PHYSICAL	

Color	White
Cable Length (ft.)	0.5
Cable Length (m)	0.15
Cable Length (in.)	6
Cable Length (cm)	15.24
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Weight (lbs.)	0.10
Shipping Weight (kg)	0.05
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
https://tripplite.eaton.com

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.