

## Keyspan Mini DisplayPort to 4K HDMI Active Adapter Video Converter, 4K 30Hz, DP1.2, (M/F), 6-in. (15.24 cm)

MODEL NUMBER: P137-06N-HD-UHD



Connect a UHD 4K x 2K HDMI monitor to a Mac or PC with a Mini Displayport output

### Features

- Connect a UHD HDMI TV to a Mac or PC with a Mini Displayport output
- Active adapter for use with any Mini Displayport (or Thunderbolt 1 & 2) port
- Converts Single-Mode and Dual-Mode (DP++) Mini DisplayPort output
- Perfect for use with graphics cards, such as AMD Eyefinity, that do not output DP++ signals
- Displayport 1.2 and HDMI 1.4 compliant
- Plug-and-play convenience—no drivers or software needed
- Supports Ultra High Definition (UHD) video resolutions up to 4K x 2K (3840 x 2160) @ 24/30 Hz
- HDCP compliant
- The P137-06N-HD-UHD supports transmission of an audio signal as long as it is supported by the Mini Displayport source-check the documentation for your Mini Displayport source for compatibility.

### Highlights

- Connect a UHD HDMI monitor to a Mac or PC with a Mini Displayport output
- Active adapter for use with any Mini Displayport (or Thunderbolt 1 & 2) port
- Plug-and-play convenience—no drivers or software needed
- Supports Ultra High Definition (UHD) video resolutions up to 4Kx2K, 3840 x 2160 (24Hz or 30Hz)
- HDCP compliant

### System Requirements

- Computer with a Mini Displayport (or Thunderbolt 1 & 2) port
- Monitor with a HDMI port.
- Both monitor and source must support 4Kx2K (24Hz or 30Hz) in order to display 4Kx2K video resolutions
- 7.1 Audio Surround Sound is supported as long as it is supported by the source. Check your Mini Displayport source documentation for compatibility.
- The P137-06N-HD-UHD is an Active adapter, and requires that the connected computer has a DP++ ( Displayport ++ ) port, which allows HDMI and DVI signals to be passed through; check the documentation for your Mini Displayport source for compatibility.



#### Package Includes

- P137-06N-HD-UHD Keyspan  
Mini DisplayPort 1.2 to UHD 4K  
HDMI Active Adapter/Video  
Converter (M/F), 6 in.

## Specifications

OVERVIEW	
UPC Code	037332183910
Technology	HDMI; DisplayPort
VIDEO	
Max Supported Color Depth	36-bit Deep Color
INPUT	
Cable Length (ft.)	0.5
Cable Length (m)	0.2
Cable Length (in.)	6
Cable Length (cm)	15.24
PHYSICAL	
Color	White
Shipping Dimensions (hwd / cm)	22.86 x 1.27 x 17.78
Shipping Dimensions (hwd / in.)	9.00 x 0.50 x 7.00
Shipping Weight (kg)	0.12
Shipping Weight (lbs.)	0.26
CONNECTIONS	
Side A - Connector 1	MINI DISPLAYPORT (MALE)
Side B - Connector 1	HDMI (FEMALE)
WARRANTY	
Product Warranty Period (Worldwide)	3-year limited warranty



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>