

Keyspan Mini DisplayPort to VGA/DVI/HDMI All-in-One Adapter Video Converter, Black, 6 in.

MODEL NUMBER: P137-06N-HDV



Features

- Connect a VGA, DVI or HDMI monitor to a Mini DisplayPort on your laptop or tablet
- All-in-One converter offers maximum flexibility to connect to any available monitor
- Portable design with built-in cable is perfect for travel and stowing in your laptop bag
- Supports computer video resolutions up to 1920 x 1200 or HD video resolutions up to 1920 x 1080 (1080p)
- Supports up to 36-bit Deep Color (12 bits per channel)
- 7.1 Audio Surround Sound only supported by HDMI
- Compatible with Thunderbolt 1 and 2 ports on Mac computers such as the MacBook Pro and MacBook Air
- Passive adapter requires the connected computer to have a DP++ (DisplayPort ++) port

Specifications

OVERVIEW	
UPC Code	037332185402
Product Type	Video Adapter
Technology	DVI; HDMI; VGA/SVGA; DisplayPort
INPUT	
Product Length (in.)	6.00
CONNECTIONS	
Side A - Connector 1	MINI DISPLAYPORT (MALE)
Side B - Connector 1	DVI-D DUAL LINK (FEMALE)

Highlights

- Connect a VGA, DVI or HDMI monitor to a Mini DisplayPort on your laptop or tablet
- All-in-one converter offers maximum flexibility to connect to any available monitor
- Passive adapter requires the connected computer to have a DP++ (DisplayPort ++) port
- Plug-and-play operation with no software required for easy, immediate installation

System Requirements

- Requires the connected computer to have a DP++ (DisplayPort ++) port
- Monitor with a VGA, DVI or HDMI port
- Not for use with MST Hubs. For compatibility with MST Hubs, use a DisplayPort-1.2-compliant product, such as P137-06N-HDV-4K

Package Includes

Mini Displayport to VGA / DVI / HDMI All-in-One Adapter / Converter, 6 in.

Side B - Connector 2	HD15 (FEMALE)
Side B - Connector 3	HDMI (FEMALE)
PHYSICAL	
Color	Black
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Weight (lbs.)	0.13
Shipping Weight (kg)	0.06
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.