

## Keyspan Mini DisplayPort to VGA/DVI/HDMI All-in-One Video Converter Adapter, 4K 30Hz HDMI, DP1.2, White, 6-in. (15.24 cm)

MODEL NUMBER: P137-06N-HDV4KW



Passive Mini DP to HDMI/VGA/DVI adapter connects your Mini DP or Thunderbolt 1/2 laptop to a VGA, DVI or HDMI display.

### Features

**Passive Adapter Connects a Mini DisplayPort Device to a VGA, DVI or HDMI Display**No more carrying around separate adapters for various monitors, projectors and televisions. This Keyspan® Mini DP to HDMI/VGA/DVI adapter connects a VGA, DVI or HDMI display to the Mini DisplayPort or Thunderbolt 1/2 port on your Chromebook, MacBook, Microsoft Surface or other compatible laptop or tablet. Only one display can be connected at a time.

**Simple All-in-One Solution for Displaying 4K Video on a Large Screen**The P137-06N-HDV4KW is ideal for classrooms, lecture halls and anywhere else you may need to connect to a monitor. Just connect the converter between your laptop and a VGA, DVI or HDMI display. You no longer have to dig around in your laptop bag for the correct adapter to match the display.

**Transmits Crystal-Clear Video up to 4K x 2K for Ultra HD Presentations**This all-in-one unit features separate female HD15, DVI and HDMI ports. The HD15 port supports high-definition video resolutions up to 1920 x 1200, including 1080p. The DVI-I dual-link port supports HD resolutions up to 1920 x 1080 (1080p). The HDMI port supports Ultra HD 4K x 2K video (3840 x 2160) at 24/30 Hz, as well as 36-bit Deep Color (12 bits per channel). The HDMI port is backward compatible with non-4K displays.

**Passive Adapter for Use with Dual-Mode DisplayPort Sources**The P137-06N-HDV4KW is a passive adapter that requires the connected computer to support DisplayPort++ (DP++). This allows HDMI and DVI signals to be passed through. Check the documentation for your Mini DisplayPort source for compatibility.

**Ready to Use Right from the Package, So You Can Plug and Play Immediately**The plug-and-play adapter requires no software, drivers or external power, works with both Windows and Mac operating systems, and is compatible with laptops, tablets and other devices equipped with a female Mini DisplayPort or Thunderbolt 1/2 port. With its small size and built-in cable, the P137-06N-HDV4KW is recommended for stowing in your laptop bag and carrying to school or the office.

**3-Year Warranty**The P137-06N-HDV4KW is backed by a 3-year warranty, ensuring reliability and performance.

### Highlights

- Multiple video outputs connect to most displays—no more carrying multiple adapters
- HDMI port delivers UHD quality at resolutions up to 3840 x 2160 (4K x 2K) @ 24/30 Hz
- Compact unit fits easily into briefcase or laptop bag for instant use anywhere
- Plug-and-play operation with no software required for easy, immediate installation
- Passive adapter requires connected computer to have DP++ port for signal pass-through

### Applications

- Connect your laptop to an HDMI, VGA or DVI monitor in a lecture hall or conference room for a video presentation
- Add a secondary monitor to the PC or laptop in your office or home workspace

### System Requirements

- Source device with Thunderbolt 1/2 output or Mini DisplayPort that supports DP++
- Display device with VGA, DVI or HDMI input

### Package Includes

- P137-06N-HDV4KW Keyspan Mini DisplayPort 1.2 to VGA/DVI/HDMI All-in-One Converter Adapter, White
- Quick Start Guide

## Specifications

<b>OVERVIEW</b>	
UPC Code	037332210630
Technology	DVI; HDMI; VGA/SVGA; DisplayPort
<b>PHYSICAL</b>	
Color	White
Cable Length (in.)	6
Shipping Dimensions (hwd / in.)	0.91 x 5.40 x 4.00
Shipping Dimensions (hwd / cm)	2.31 x 13.72 x 10.16
Shipping Weight (lbs.)	0.20
Shipping Weight (kg)	0.09
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	32 to 113 F (0 to 45 C)
Storage Temperature Range	14 to 176 F (-10 to 80 C)
Operating Humidity Range	10% to 85% RH, Non-Condensing
Storage Humidity Range	5% to 90% RH, Non-Condensing
<b>CONNECTIONS</b>	
Side A - Connector 1	MINI DISPLAYPORT (MALE)
Side B - Connector 1	DVI-I DUAL LINK (FEMALE)
Side B - Connector 2	HD15 (FEMALE)
Side B - Connector 3	HDMI (FEMALE)
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Compliance	RoHS; CE (Europe); REACH; FCC (USA)
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	3-year limited warranty



1000 Eaton Boulevard  
Cleveland, OH 44122  
United States



© 2023 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.