

Keyspan Mini DisplayPort to VGA/HDMI All-in-One Video Converter Adapter, 4K 30Hz HDMI, DP1.2, White, 6-in. (15.24 cm)

MODEL NUMBER: P137-06N-HV-V2W



All-in-one converter/adapter connects your Mini DisplayPort or Thunderbolt-enabled laptop or tablet to a VGA or HDMI display without the need to carry separate adapters. Ideal for trade shows, classrooms and lecture halls.

Features

Connects Your Mini DisplayPort Laptop or Tablet to a VGA or HDMI Display

- Ideal for trade shows, classrooms, lecture halls and other presentations
- HD15 port supports video resolutions up to 1920 x 1200, including 1080p
- HDMI port supports UHD video resolutions up to 3840 x 2160 (4K x 2K) @ 24/30 Hz
- Supports 36-bit Deep Color (12 bits per channel)

Plug-and-Play Convenience

- No software or drivers to install
- No external power supply required
- Small enough to stow in laptop bag or briefcase
- The P137-06N-HV-V2W is a Passive adapter, and requires the connected computer to have a DP++ (Displayport ++) port

Specifications

| OVERVIEW | |
|------------|-----------------------------|
| UPC Code | 037332193223 |
| Technology | HDMI; VGA/SVGA; DisplayPort |
| PHYSICAL | |

Highlights

- Separate HD15 and HDMI female connectors
- HDMI port supports UHD 4K x 2K @ 24/30 Hz video resolutions
- The P137-06N-HV-V2W is a Passive adapter, and requires the connected computer to have a DP++ (Displayport ++) port
- Plug and play—no software, drivers or power supply needed
- Small size for easy carrying in laptop bag or briefcase

System Requirements

- The P137-06N-HV-V2W is a Passive adapter, and requires the connected computer to have a DP++ (Displayport ++) port

Package Includes

- P137-06N-HV-V2W Keyspan Mini DisplayPort 1.2 to VGA/HDMI All-in-One Converter Adapter, 6 in.
- Owner's manual

TRIPP-LITE

by **EAT•N**

1000 Eaton Boulevard
Cleveland, OH 44122
United States

| | |
|-------------------------------------|-------------------------|
| Color | White |
| Cable Length (ft.) | 0.5 |
| Cable Length (m) | 0.15 |
| Cable Length (in.) | 6 |
| Cable Length (cm) | 15.24 |
| Shipping Dimensions (hwd / in.) | 3.90 x 4.70 x 0.50 |
| Shipping Dimensions (hwd / cm) | 9.91 x 11.94 x 1.27 |
| Shipping Weight (lbs.) | 0.15 |
| Shipping Weight (kg) | 0.07 |
| CONNECTIONS | |
| Side A - Connector 1 | MINI DISPLAYPORT (MALE) |
| Side B - Connector 1 | HD15 (FEMALE) |
| Side B - Connector 2 | HDMI (FEMALE) |
| WARRANTY & SUPPORT | |
| Product Warranty Period (Worldwide) | 3-year limited warranty |

TRIPP-LITE

by **EAT•N**

© 2023 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.