

Keyspan Mini DisplayPort to Active VGA Adapter, Video Converter (M/F), Black, 6-in. (15.24 cm), 50 pack

MODEL NUMBER: P137-06N-VGA-BP



Mini DP to VGA adapter connects a VGA monitor to the Mini DisplayPort or Thunderbolt 1/2 output on your laptop or computer.

Features

Mini DisplayPort to VGA Converters Connect Mini DP Source to VGA Display This set includes 50 P137-06N-VGA Keyspan® Mini DP to VGA active adapters. Each adapter connects a VGA monitor, projector or television to the Mini DisplayPort or Thunderbolt 1 or 2 port on your PC, Mac, Chromebook, MacBook, Microsoft Surface or other compatible computer or tablet. They feature a male Mini DP connector and a female VGA connector, allowing you to continue using your existing VGA display and VGA cable to transmit video signals without the expense of a new Mini DP display.

Transmit Outstanding 1080p Video for High-Definition Presentations Ideal for classrooms, lecture halls and anywhere else you may need to connect to a VGA monitor, these Mini DisplayPort to VGA converters support VGA computer video resolutions up to 1920 x 1200, including 1080p, and high-definition resolutions up to 1080p. The active adapters convert both Single-Mode and Dual-Mode (DP++) DisplayPort output. They come recommended for use with graphics cards, such as AMD Eyefinity, that do not output DP++ signals.

Ready to Use Right Out of the Package The plug-and-play Mini DP to VGA adapters require no software, drivers or external power, work with both Windows and Mac operating systems, and are compatible with laptops, tablets and other devices equipped with a female Mini DisplayPort or Thunderbolt 1 or 2 port. With its small size and built-in cable, the P137-06N-VGA is recommended for stowing in your laptop bag and carrying to school or the office.

Specifications

OVERVIEW	
UPC Code	037332237682
Product Type	Video Adapter

Highlights

- 50-piece bulk pack of P137-06N-VGA Mini DisplayPort to VGA video adapters
- Delivers high-definition picture quality at resolutions up to 1920 x 1200, including 1080p
- Active adapter converts Single- and Dual-Mode DP++ output for viewing on VGA display
- Compact unit fits easily into briefcase or laptop bag for instant use anywhere
- Plug-and-play operation with no software required for easy, immediate installation

Applications

- Connect your newer laptop to an older VGA monitor in a lecture hall or conference room for a video presentation
- Add a secondary monitor to the PC or laptop in your office or home workspace
- Display menus, ads, promos, directions and other digital signage applications

System Requirements

- Source device with Mini DisplayPort or Thunderbolt 1 or 2 output
- Display device with VGA input
- Not for use with MST hubs

Package Includes

- (50) P137-06N-VGA Keyspan Mini DisplayPort to VGA Active Adapters

Technology	VGA/SVGA; DisplayPort
VIDEO	
Max Supported Video Resolution	1920 x 1200 (1080p)
INPUT	
Product Length (in.)	5.9
Product Length (ft.)	0.49
PHYSICAL	
Color	White
Material of Construction	ABS, PVC
Cable Jacket Material	PVC
Cable Jacket Rating	VW-1
Cable Outer Diameter (OD)	4.5mm
Shipping Dimensions (hwd / in.)	1.00 x 15.50 x 17.50
Shipping Weight (kg)	1.50
ENVIRONMENTAL	
Operating Temperature Range	32° to 158°F (0° to 70°C)
Storage Temperature Range	14° to 176°F (-10° to 80°C)
Operating Humidity Range	10% - 85% RH, Non-Condensing
Storage Humidity Range	5% - 90% RH, Non-Condensing
CONNECTIONS	
Side A - Connector 1	MINI DISPLAYPORT (MALE)
Side B - Connector 1	HD15 (FEMALE)
Connector Plating	Nickel
Contact Plating	Gold
FEATURES & SPECIFICATIONS	
Displayport Specification	1.1
Driver Required	No
STANDARDS & COMPLIANCE	
Product Compliance	CE (Europe); FCC (USA); REACH; RoHS; UKCA; WEEE
WARRANTY & SUPPORT	



1000 Eaton Boulevard
Cleveland, OH 44122
United States

Product Warranty Period (Worldwide)	3-year limited warranty
--	-------------------------



© 2023 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.