

Keyspan Mini DisplayPort to Active VGA Adapter, Video Converter, DP1.2, (M/F), White, 6-in.

MODEL NUMBER: P137-06N-VGA-V2



Description

Tripp Lite's P137-06N-VGA-V2 Mini-DisplayPort v1.2 to VGA Active Adapter Converter allows you to connect a computer with a Mini-DisplayPort or Thunderbolt™ 1 & 2 connection to a VGA monitor.

Ideal for Thunderbolt™ /Mini DisplayPort equipped laptops, Chromebooks, MacBooks and Microsoft Surface.

DisplayPort v1.2 doubles the previous version bandwidth of 8.64 Gbps to 17.28 Gbps in High Bit Rate (HBR2) mode, which allows increased resolutions, higher refresh rates, and greater color depth.

Supports VGA computer video resolutions up to 1920 x 1200 and HD resolutions up to 1080p. Unlike passive adapters, Active adapters convert both Single-Mode and

Dual Mode (DP++) DisplayPort output. It is ideal for use with graphics cards, such as AMD Eyefinity, that do not output Dual Mode (DP++) signals.

Features

- Connect a VGA monitor to a computer with a Mini-DisplayPort or Thunderbolt 1/2 output
- Mini-DisplayPort v1.2 to VGA Active Adapter Converter (Mini-DisplayPort Male to VGA Female)
- Supports VGA computer video resolutions up to 1920 x 1200 and HD resolutions up to 1080p
- 17.28 Gbps bandwidth

Highlights

- Connect a VGA monitor to a computer with a Mini-DisplayPort or Thunderbolt 1/2 output
- Mini-DisplayPort v1.2 to VGA Active Adapter Converter (Mini-DisplayPort Male to VGA Female)
- Plug-and-play convenience; no drivers or software needed
- Ideal for use with graphics cards, such as AMD Eyefinity, that do not output Dual Mode (DP++) signals
- Converts both Single-Mode and Dual Mode (DP++) Displayport output

Package Includes

- Mini-DisplayPort 1.2 to VGA Active Adapter Converter (Mini-DP Male to VGA Female) 6-in.



- Plug and Play; no drivers or software require
- Ideal for use with graphics cards, such as AMD Eyefinity, that do not output Dual Mode (DP++) signals
- Converts both Single-Mode and Dual Mode (DP++) Displayport output

Specifications

OVERVIEW	
UPC Code	037332187543
INPUT	
Cable Length (ft.)	0.5
Cable Length (m)	0.2
Cable Length (in.)	6
Cable Length (cm)	15.24
PHYSICAL	
Color	White
Shipping Dimensions (hwd / cm)	1.27 x 17.78 x 22.86
Shipping Dimensions (hwd / in.)	0.50 x 7.00 x 9.00
Shipping Weight (kg)	0.03
Shipping Weight (lbs.)	0.07
CONNECTIONS	
Side A - Connector 1	MINI DISPLAYPORT (MALE)
Side B - Connector 1	HD15 (FEMALE)
FEATURES & SPECIFICATIONS	
Technology	VGA/SVGA; DisplayPort
WARRANTY	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>