

HDMI Right Angle Up Adapter/Coupler (M/F), 4K @ 60Hz

MODEL NUMBER: P142-000-UP



Highlights

- Use in tight spaces where cables would not ordinarily fit
- Saves wear and tear on equipment ports and cable ends

System Requirements

- Video equipment with HDMI video out ports

Package Includes

- HDMI Male to Female Right Angle adapter

Description

The 90-degree angle of this adapter allows you to reposition the HDMI jack for better access where space is tight. This adapter also offers a great way to protect your HDMI cables and equipment from strain and damage, since HDMI cables have relatively small connectors and jacks that must bear the brunt of the cable's weight. The plug-and-play design makes installation a breeze. The P142-000-UP Right Angle HDMI Adapter features gold-plated connectors for optimal signal transmission quality. Provides clean, uncompressed digital signals. Supports video resolution up to 4K x 2K (3840 x 2160) @ 60Hz.

Features

- HDMI Male Plug
- HDMI Female Jack
- One inch deep when plugged into video port
- Supports video resolution up to 4K x 2K (3840 x 2160) @ 60Hz.

Specifications

OVERVIEW	
UPC Code	037332164698
Technology	HDMI
PHYSICAL	
Color	Black
Shipping Dimensions (hwd / in.)	5.30 x 3.90 x 0.50
Shipping Dimensions (hwd / cm)	13.46 x 9.91 x 1.27
Shipping Weight (lbs.)	0.03

Shipping Weight (kg)	0.01
CONNECTIONS	
Side A - Connector 1	HDMI (FEMALE)
Side B - Connector 1	HDMI (MALE)
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; REACH
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty