



HDMI Right Angle Up Adapter/Coupler (M/F), 4K @ 60Hz

MODEL NUMBER: P142-000-UP





Description

The 90-degree angle of this adapter allows you to reposition the HDMI jack for better access where space is tight. This adapter also offers a great way to protect your HDMI cables and equipment from strain and damage, since HDMI cables have relatively small connectors and jacks that must bear the brunt of the cable's weight. The plug-and-play design makes installation a breeze. The P142-000-UP Right Angle HDMI Adapter features gold-plated connectors for optimal signal transmission quality. Provides clean, uncompressed digital signals. Supports video resolution up to 4K x 2K (3840 x 2160) @ 60Hz.

Features

- HDMI Male Plug
- HDMI Female Jack
- One inch deep when plugged into video port
- Supports video resolution up to 4K x 2K (3840 x 2160) @ 60Hz.

Specifications

OVERVIEW		
UPC Code	037332164698	
Product Type	Video Adapter	
Technology	HDMI	
CONNECTIONS		
Side A - Connector 1	HDMI (FEMALE)	
Side B - Connector 1	HDMI (MALE)	
PHYSICAL		

Highlights

- Use in tight spaces where cables would not ordinarily fit
- Saves wear and tear on equipment ports and cable ends

System Requirements

 Video equipment with HDMI video out ports

Package Includes

• HDMI Male to Female Right Angle adapter





Color	Black	
Shipping Dimensions (hwd / in.)	5.30 x 3.90 x 0.50	
Shipping Dimensions (hwd / cm)	13.46 x 9.91 x 1.27	
Shipping Weight (lbs.)	0.03	
Shipping Weight (kg)	0.01	
FEATURES & SPECIFICATIONS		
IP68 Rated	No	
IP20 Rated	No	
STANDARDS & COMPLIANCE		
Product Compliance	RoHS; REACH; WEEE	
WARRANTY & SUPPORT		
Product Warranty Period (Worldwide)	Lifetime limited warranty	

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.