

## 3.5mm Mini Stereo Audio Cable for Microphones, Speakers and Headphones (M/M), 12 ft. (3.66 m)

MODEL NUMBER: P312-012



### Highlights

- Connect mini stereo audio equipment
- Perfect for use with mobile devices such as iPod, iPhone, and MP3 players
- Molded cables with built-in strain relief
- Gold plated connectors ensure excellent conductivity

### Package Includes

- 12-ft. (3.66 m) 3.5mm Mini Stereo Audio Cable (M/M)

### Description

12-ft. (3.66 m) Mini Stereo Audio cable for microphones, speakers, headphones, and other audio devices. Perfect for use with mobile devices such as iPod, iPhone, and MP3 players. Gold plated connectors ensure excellent conductivity.

### Features

- Connect mini stereo audio equipment
- Perfect for use with mobile devices such as iPod, iPhone, and MP3 players
- Molded cables with built-in strain relief
- Gold plated connectors ensure excellent conductivity

## Specifications

| OVERVIEW                       |              |
|--------------------------------|--------------|
| UPC Code                       | 037332187802 |
| Technology                     | Stereo Audio |
| Cable Type                     | Passive      |
| CONNECTIONS                    |              |
| Side A - Connector 1           | 3.5MM (MALE) |
| Side B - Connector 1           | 3.5MM (MALE) |
| Latching or Gripping Connector | No           |
| PHYSICAL                       |              |
| Color                          | Black        |



Powering Business Worldwide

TRIPP LITE  
SERIES

|                                      |                           |
|--------------------------------------|---------------------------|
| Cable Jacket Color                   | Black                     |
| Cable Length (ft.)                   | 12                        |
| Cable Length (m)                     | 3.66                      |
| Shipping Dimensions (hwd / in.)      | 9.00 x 7.00 x 0.50        |
| Shipping Dimensions (hwd / cm)       | 22.86 x 17.78 x 1.27      |
| Shipping Weight (lbs.)               | 0.10                      |
| Shipping Weight (kg)                 | 0.05                      |
| <b>FEATURES &amp; SPECIFICATIONS</b> |                           |
| IP68 Rated                           | No                        |
| IP20 Rated                           | No                        |
| <b>STANDARDS &amp; COMPLIANCE</b>    |                           |
| Product Compliance                   | RoHS                      |
| <b>WARRANTY &amp; SUPPORT</b>        |                           |
| Product Warranty Period (Worldwide)  | Lifetime limited warranty |

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.