

## 3.5 mm 3-Position to 3.5 mm 4-Position Audio Headset Splitter Adapter Cable (2xF/M), 6 in. (15.2 cm)

MODEL NUMBER: P318-06N-MFF



### Highlights

- Splits the 4-Position combo audio jack on your computer, laptop or mobile device into separate speaker and microphone jacks
- Allows for the connection of a set of speakers and microphone to a single 4-Position combo audio jack
- Molded cables with built-in strain relief

### Package Includes

- 6-in. 4-Position Male to (x2) 3-Position Female Audio Adapter Cable

Connect a set of speakers and microphone to the 4-position combo audio jack on your computer, laptop or mobile device

### Features

- Splits the 4-Position combo audio jack on your computer, laptop or mobile device into separate speaker and microphone jacks
- Allows for the connection of a set of speakers and microphone to a single 4-Position combo audio jack
- Molded cables with built-in strain relief
- Constructed of 28AWG wire
- Features a compact design perfect for tucking into your laptop bag when you're on the go

## Specifications

OVERVIEW	
UPC Code	037332184047
Product Type	Passive Cable
Technology	Stereo Audio
Cable Type	Passive
PHYSICAL	
Color	Black
Cable Jacket Color	Black
Cable Length (ft.)	0.5

Cable Length (m)	0.15
Cable Length (in.)	6
Cable Length (cm)	15.24
Shipping Dimensions (hwd / in.)	7.00 x 9.00 x 0.50
Shipping Dimensions (hwd / cm)	17.78 x 22.86 x 1.27
Shipping Weight (lbs.)	0.08
Shipping Weight (kg)	0.04
<b>CONNECTIONS</b>	
Side A - Connector 1	3.5MM (MALE)
Side B - Connector 1	(2) 3.5MM (FEMALE)
Latching or Gripping Connector	No
<b>FEATURES &amp; SPECIFICATIONS</b>	
IP68 Rated	No
IP20 Rated	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Compliance	RoHS
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty