

## VGA High-Resolution RGB Coaxial Cable (HD15 M/F), 6 ft. (1.83 m)

MODEL NUMBER: P500-006



Extend the high-resolution connection between your VGA-enabled computer and monitor up to 6 ft. with no ghosting. Recommended for easy access to VGA ports that are hidden or hard to reach.

### Features

#### Extends Connection Between VGA-Enabled Computer and Monitor Up to 6 ft.

- Supports video resolutions up to 2048 x 1536, including 1080p
- Made from mini-coax (RGB) and paired video wire
- Foil and braid shielding protects against EMI/RFI line noise that can distort or destroy data
- Molded gold-plated HD15 connectors and contacts provide maximum conductivity and minimize data loss
- Integral strain relief protects cable and connectors from stress and cracking
- Rugged PVC jacket designed for long life

## Specifications

OVERVIEW	
UPC Code	037332012296
Product Type	Passive Cable
Technology	Coax; VGA/SVGA
Cable Type	Passive
PHYSICAL	
Color	Black
Cable Jacket Color	Black
Cable Length (ft.)	6

### Highlights

- Supports video resolutions up to 2048 x 1536, including 1080p
- Made from mini-coax (RGB) and paired video wire
- Foil and braid shielding blocks hazardous EMI/RFI line noise
- Gold-plated connectors and contacts for maximum conductivity
- Integral strain relief protects against cable stress and cracking

### System Requirements

- Display device with HD15 input

### Package Includes

- P500-006 VGA Coax High-Resolution Monitor Extension Cable (M/F), 6 ft.

Cable Length (m)	1.83
Cable Length (in.)	72
Shipping Dimensions (hwd / in.)	7.00 x 9.00 x 0.50
Shipping Dimensions (hwd / cm)	17.78 x 22.86 x 1.27
Shipping Weight (lbs.)	0.58
Shipping Weight (kg)	0.26
<b>CONNECTIONS</b>	
Side A - Connector 1	HD15 (MALE)
Side B - Connector 1	HD15 (FEMALE)
Latching or Gripping Connector	No
<b>FEATURES &amp; SPECIFICATIONS</b>	
IP68 Rated	No
IP20 Rated	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Compliance	RoHS
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty