



VGA High-Resolution RGB Coaxial Cable (HD15 M/M), 6 ft. (1.83 m)

MODEL NUMBER: P502-006



Allows a high-resolution connection between your VGA-enabled computer and monitor up to 6 ft. apart with no ghosting.

Features

Allows Connection Between VGA-Enabled Computer and Monitor Up to 6 ft.

- Supports video resolutions up to 2048 x 1536, including 1080p
- Made from mini-coaxial (RGB) and paired video wire
- Foil and braid shielding protects against EMI/RFI line noise that can distort or destroy data
- Molded gold-plated HD15 male connectors and contacts provide maximum conductivity and minimize data loss
- Integral strain relief protects cable and connectors from stress and cracking
- Rugged PVC jacket designed for long life

Specifications

OVERVIEW		
UPC Code	037332012319	
Product Type	Passive Cable	
Technology	Coax; VGA/SVGA	
Cable Type	Passive	
CONNECTIONS		
Side A - Connector 1	HD15 (MALE)	
Side B - Connector 1	HD15 (MALE)	
Latching or Gripping Connector	No	

Highlights

- Supports video resolutions up to 2048 x 1536, including 1080p
- Made from mini-coaxial (RGB) and paired video wire
- Foil and braid shielding blocks hazardous EMI/RFI line noise
- Gold-plated connectors and contacts for maximum conductivity
- Integral strain relief protects against cable stress and cracking

System Requirements

- Display device with HD15 input
- Computer with HD15 output

Package Includes

 P502-006 VGA Coaxial High-Resolution Monitor Cable (M/M), 6 ft.





PHYSICAL		
Color	Black	
Cable Jacket Color	Black	
Cable Length (ft.)	6	
Cable Length (m)	1.83	
Cable Length (in.)	72	
Shipping Dimensions (hwd / in.)	7.00 x 9.00 x 0.50	
Shipping Dimensions (hwd / cm)	17.78 x 22.86 x 1.27	
Shipping Weight (lbs.)	0.59	
Shipping Weight (kg)	0.27	
FEATURES & SPECIFICATIONS		
IP68 Rated	No	
IP20 Rated	No	
STANDARDS & COMPLIANCE		
Product Compliance	RoHS	
WARRANTY & SUPPORT		
Product Warranty Period (Worldwide)	Lifetime limited warranty	

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark. All other trademarks are the property of their respective owners.