

VGA High-Resolution RGB Coaxial Cable (HD15 M/M), 6 ft. (1.83 m)

MODEL NUMBER: P502-006



Allows a high-resolution connection between your VGA-enabled computer and monitor up to 6 ft. apart with no ghosting.

Features

Allows Connection Between VGA-Enabled Computer and Monitor Up to 6 ft.

- Supports video resolutions up to 2048 x 1536, including 1080p
- Made from mini-coaxial (RGB) and paired video wire
- Foil and braid shielding protects against EMI/RFI line noise that can distort or destroy data
- Molded gold-plated HD15 male connectors and contacts provide maximum conductivity and minimize data loss
- Integral strain relief protects cable and connectors from stress and cracking
- Rugged PVC jacket designed for long life

Specifications

| OVERVIEW | |
|--------------------------------|----------------|
| UPC Code | 037332012319 |
| Product Type | Passive Cable |
| Technology | Coax; VGA/SVGA |
| Cable Type | Passive |
| CONNECTIONS | |
| Side A - Connector 1 | HD15 (MALE) |
| Side B - Connector 1 | HD15 (MALE) |
| Latching or Gripping Connector | No |

Highlights

- Supports video resolutions up to 2048 x 1536, including 1080p
- Made from mini-coaxial (RGB) and paired video wire
- Foil and braid shielding blocks hazardous EMI/RFI line noise
- Gold-plated connectors and contacts for maximum conductivity
- Integral strain relief protects against cable stress and cracking

System Requirements

- Display device with HD15 input
- Computer with HD15 output

Package Includes

- P502-006 VGA Coaxial High-Resolution Monitor Cable (M/M), 6 ft.



Powering Business Worldwide

TRIPP LITE
SERIES

| PHYSICAL | |
|-------------------------------------|---------------------------|
| Color | Black |
| Cable Jacket Color | Black |
| Cable Length (ft.) | 6 |
| Cable Length (m) | 1.83 |
| Cable Length (in.) | 72 |
| Shipping Dimensions (hwd / in.) | 7.00 x 9.00 x 0.50 |
| Shipping Dimensions (hwd / cm) | 17.78 x 22.86 x 1.27 |
| Shipping Weight (lbs.) | 0.59 |
| Shipping Weight (kg) | 0.27 |
| FEATURES & SPECIFICATIONS | |
| IP68 Rated | No |
| IP20 Rated | No |
| STANDARDS & COMPLIANCE | |
| Product Compliance | RoHS |
| WARRANTY & SUPPORT | |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.