

## VGA High-Resolution RGB Coaxial Cable (HD15 M/M), Right-Angle Connector), 25 ft. (7.62 m)

MODEL NUMBER: P502-025-RA



Allows a high-resolution connection between your VGA-enabled computer and monitor up to 25 ft. apart with no ghosting.

### Description

The P502-025-RA VGA Coaxial High-Resolution Monitor Cable (M/M) allows you to connect your VGA-enabled computer and monitor up to 25-ft. (7.62 m) apart. Constructed from mini-coaxial (RGB) and paired video wire, it supports video resolutions up to 2048 x 1536, including 1080p, with no ghosting. One HD15 connector is fixed at a 90-degree angle to allow more room for the cable and allow equipment to be pushed flush against a wall.

Foil and braid shielding delivers reliable, error-free signal quality and protection from EMI/RFI line noise that can distort or destroy data. Molded gold-plated HD15 male connectors with gold-plated contacts provide maximum conductivity and minimize data loss. Integral strain relief gives the cable extra flexibility, reduces stress, and helps the cable and connectors move freely without cracking.

### Features

#### Allows Connection Between VGA-Enabled Computer and Monitor Up to 25-ft. (7.62 m)

- Supports video resolutions up to 2048 x 1536, including 1080p
- Right-angle connector allows more room for connecting in tight spaces and moving connected equipment against a wall
- Made from mini-coaxial (RGB) and paired video wire
- Foil and braid shielding protects against EMI/RFI line noise that can distort or destroy data
- Molded gold-plated HD15 male connectors and contacts provide maximum conductivity and minimize data loss
- Integral strain relief protects cable and connectors from stress and cracking
- Rugged PVC jacket designed for long life

### Highlights

- Supports video resolutions up to 2048 x 1536, including 1080p
- Made from mini-coaxial (RGB) and paired video wire
- Foil and braid shielding blocks hazardous EMI/RFI line noise
- Gold-plated connectors and contacts for maximum conductivity
- Right-angle HD15 connector easy to connect in tight spaces

### System Requirements

- Display device with HD15 input
- Computer with HD15 output

### Package Includes

- P502-025-RA VGA Coaxial High-Resolution Monitor Cable (M/M), 25-ft. (7.62 m)



## Specifications

OVERVIEW	
UPC Code	037332147363
Technology	Coax; VGA/SVGA
PHYSICAL	
Color	Black
Cable Length (ft.)	25
Cable Length (m)	7.6
Shipping Dimensions (hwd / cm)	30.48 x 25.40 x 1.27
Shipping Dimensions (hwd / in.)	12.00 x 10.00 x 0.50
Shipping Weight (kg)	0.68
Shipping Weight (lbs.)	1.50
CONNECTIONS	
Side A - Connector 1	HD15 (MALE) - RIGHT ANGLE
Side B - Connector 1	HD15 (MALE)
FEATURES & SPECIFICATIONS	
Cable Style	Passive
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>