

VGA High-Resolution RGB Coaxial Cable (HD15 M/M), 75 ft. (22.86 m)

MODEL NUMBER: P502-075



Allows a high-resolution connection between your VGA-enabled computer and monitor up to 75 ft. apart with no ghosting.

Description

The P502-075 VGA Coaxial High-Resolution Monitor Cable (M/M) allows you to connect your VGA-enabled computer and monitor up to 75-ft. (22.86 m) apart. Constructed from mini-coaxial (RGB) and paired video wire, it supports video resolutions up to 2048 x 1536, including 1080p, with no ghosting. Foil and braid shielding delivers reliable, error-free signal quality and protection from EMI/RFI line noise that can distort or destroy data. Molded gold-plated HD15 male connectors with gold-plated contacts provide maximum conductivity and minimize data loss. Integral strain relief gives the cable extra flexibility, reduces stress, and helps the cable and connectors move freely without cracking.

Features

Allows Connection Between VGA-Enabled Computer and Monitor Up to 75-ft. (22.86 m)

- Supports video resolutions up to 2048 x 1536, including 1080p
- Made from mini-coaxial (RGB) and paired video wire
- Foil and braid shielding protects against EMI/RFI line noise that can distort or destroy data
- Molded gold-plated HD15 male connectors and contacts provide maximum conductivity and minimize data loss
- Integral strain relief protects cable and connectors from stress and cracking
- Rugged PVC jacket designed for long life

Specifications

| OVERVIEW | |
|--------------|----------------|
| UPC Code | 037332176547 |
| Product Type | Passive Cable |
| Technology | Coax; VGA/SVGA |
| Cable Type | Passive |

Highlights

- Supports video resolutions up to 2048 x 1536, including 1080p
- Made from mini-coaxial (RGB) and paired video wire
- Foil and braid shielding blocks hazardous EMI/RFI line noise
- Gold-plated connectors and contacts for maximum conductivity
- Integral strain relief protects against cable stress and cracking

System Requirements

- Display device with HD15 input
- Computer with HD15 output

Package Includes

- P502-075 VGA Coaxial High-Resolution Monitor Cable (M/M), 75-ft. (22.86 m)



Powering Business Worldwide

TRIPP LITE
SERIES

| CONNECTIONS | |
|-------------------------------------|---------------------------|
| Side A - Connector 1 | HD15 (MALE) |
| Side B - Connector 1 | HD15 (MALE) |
| Latching or Gripping Connector | No |
| PHYSICAL | |
| Color | Black |
| Cable Jacket Color | Black |
| Cable Length (ft.) | 75 |
| Cable Length (m) | 22.87 |
| Cable Length (in.) | 900 |
| Shipping Dimensions (hwd / in.) | 14.00 x 17.00 x 1.00 |
| Shipping Dimensions (hwd / cm) | 35.56 x 43.18 x 2.54 |
| Shipping Weight (lbs.) | 5.40 |
| Shipping Weight (kg) | 2.45 |
| FEATURES & SPECIFICATIONS | |
| IP68 Rated | No |
| STANDARDS & COMPLIANCE | |
| Product Compliance | RoHS |
| WARRANTY & SUPPORT | |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.