

## VGA High-Resolution RGB Coaxial Cable with Audio (HD15 and 3.5mm M/M) 6 ft. (1.83 m)

MODEL NUMBER: **P504-006**



### Highlights

- Superior molded cables with foil-shielding for maximum EMI/RFI protection
- VW-1 and CM Rated Jacketing
- 3.5mm Stereo Plugs

### Package Includes

- 6-ft. (1.83 m) SVGA/VGA Monitor Cable HD15M to HD15M w/Built-in Audio connectors

### Description

This PVC SVGA/VGA monitor replacement cable features built-in 3.5 mm stereo plugs for extending audio and video. The mini-coax (RGB) and paired video wire construction delivers superior video signal quality. Nickel-plated connectors and gold-plated copper contacts ensure excellent conductivity. Double shielding (foil and braid) provides maximum EMI/RFI protection. Both high-density DB15 male connectors are molded and have integral strain relief to ensure they last a long time.

### Features

- Extend both Video and Audio signals
- Superior molded cables with foil-shielding for maximum EMI/RFI protection
- Constructed from mini-coax (RGB) and paired video wire construction for superior signal quality.
- HD15 male to HD15 male molded connectors
- Computer side Audio Pigtail: 8in Display side Audio Pigtail: 24in
- VW-1 and CM Rated Jacketing

## Specifications

OVERVIEW	
UPC Code	037332160058
Product Type	Passive Cable
Technology	Coax; VGA/SVGA; Stereo Audio
Cable Type	Passive
CONNECTIONS	
Side A - Connector 1	HD15 (MALE)
Side A - Connector 2	3.5MM (MALE)



Powering Business Worldwide

TRIPP LITE  
SERIES

Side B - Connector 1	HD15 (MALE)
Side B - Connector 2	3.5MM (MALE)
Latching or Gripping Connector	No
<b>PHYSICAL</b>	
Color	Black
Cable Jacket Color	Black
Cable Length (ft.)	6
Cable Length (m)	1.83
Cable Length (in.)	72
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Weight (lbs.)	0.60
Shipping Weight (kg)	0.27
Unit Dimensions (hwd / in.)	0.000 x 0.000 x 0.000
<b>FEATURES &amp; SPECIFICATIONS</b>	
IP68 Rated	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Compliance	RoHS
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.