



Low-Profile VGA High-Resolution RGB Coaxial Cable with Audio, (HD15 and 3.5mm M/M), 6 ft. (1.83 m)

MODEL NUMBER: P504-006-SM





Highlights

- Slim, compact SVGA / VGA Male-Male Cable with Audio, 6ft. (1.83 m)
- 40% thinner cable than standard VGA Cables
- More compact molded ends
- Supports up to 2048x1536 Resolution
- VW-1 Rated Jacketing

Package Includes

 6-ft. (1.83 m), Compact SVGA / VGA M/M Monitor Cable with Audio Cable

Description

This PVC, SVGA / VGA compact monitor replacement cable features a 40% reduced diameter, smaller molded connectors and built-in 3.5 mm stereo plugs for extending audio as well as video. The mini-coax (RGB) and paired video wire construction delivers superior video signal quality up to 2048 x 1536. Nickel-plated connectors and gold-plated copper contacts ensure excellent conductivity. Double shielding (foil and braid) provides maximum EMI/RFI protection. Both high-density DB15 male connectors are molded and have integral strain relief to ensure long life.

Features

- Slim, compact SVGA / VGA Male Male Cable with Audio, 6ft
- 40% thinner cable than standard VGA Cables
- Smaller, more compact, molded ends than standard VGA cables
- Supports up to 2048x1536 Resolution
- 22-inch Audio 3.5mm Stereo pigtails
- Foil and Braid shielded for superior noise suppression
- VW-1 Rated Jacketing

Specifications

OVERVIEW		
UPC Code	037332163332	
Product Type	Passive Cable	
Technology	Coax; VGA/SVGA; Stereo Audio	
Cable Type	Passive	
CONNECTIONS		





Side A - Connector 1	HD15 (MALE) - LOW PROFILE	
Side A - Connector 2	3.5MM (MALE)	
Side B - Connector 1	HD15 (MALE) - LOW PROFILE	
Side B - Connector 2	3.5MM (MALE)	
Latching or Gripping Connector	No	
PHYSICAL		
Color	Black	
Cable Jacket Color	Black	
Cable Length (ft.)	6	
Cable Length (m)	1.83	
Cable Length (in.)	72	
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50	
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27	
Shipping Weight (lbs.)	0.23	
Shipping Weight (kg)	0.10	
FEATURES & SPECIFICATIONS		
IP68 Rated	No	
STANDARDS & COMPLIANCE		
Product Compliance	RoHS	
WARRANTY & SUPPORT		
Product Warranty Period (Worldwide)	Lifetime limited warranty	

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark. All other trademarks are the property of their respective owners.