

## VGA High-Resolution RGB Coaxial Cable with Audio (HD15 and 3.5mm M/M), 10 ft. (3.05 m)

MODEL NUMBER: P504-010



### Highlights

- Superior molded cables with foil-shielding for maximum EMI/RFI protection
- VW-1 and CM Rated Jacketing
- 3.5mm Stereo Plugs

### Package Includes

- 10-ft. SVGA/VGA Monitor Cable HD15M to HD15M w/Built-in Audio connectors

### Features

- Extend both Video and Audio signals
- Superior molded cables with foil-shielding for maximum EMI/RFI protection
- Constructed from mini-coax (RGB) and paired video wire construction for superior signal quality.
- HD15 male to HD15 male molded connectors
- Computer side Audio Pigtail: 8in Display side Audio Pigtail: 24in
- VW-1 and CM Rated Jacketing

## Specifications

OVERVIEW	
UPC Code	037332135797
Product Type	Passive Cable
Technology	Coax; VGA/SVGA; Stereo Audio
Cable Type	Passive
PHYSICAL	
Color	Black
Cable Jacket Color	Black
Cable Length (ft.)	10
Cable Length (m)	3.05
Cable Length (in.)	120

Shipping Dimensions (hwd / in.)	10.00 x 8.00 x 0.50
Shipping Dimensions (hwd / cm)	25.40 x 20.32 x 1.27
Shipping Weight (lbs.)	0.80
Shipping Weight (kg)	0.36
Unit Dimensions (hwd / in.)	10.000 x 8.000 x 0.500
<b>CONNECTIONS</b>	
Side A - Connector 1	HD15 (MALE)
Side A - Connector 2	3.5MM (MALE)
Side B - Connector 1	HD15 (MALE)
Side B - Connector 2	3.5MM (MALE)
Latching or Gripping Connector	No
<b>FEATURES &amp; SPECIFICATIONS</b>	
IP68 Rated	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Compliance	RoHS
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty