

VGA High-Resolution RGB Coaxial Cable with Audio (HD15 and 3.5mm M/M), 25 ft. (7.62 m)

MODEL NUMBER: P504-025



Highlights

- Superior molded cables with foil-shielding for maximum EMI/RFI protection
- VW-1 and CM Rated Jacketing
- 3.5mm Stereo Plugs

Package Includes

- 25-ft. (7.62 m) SVGA/VGA Monitor Cable HD15M to HD15M w/Built-in Audio connectors

Description

Tripp Lite's 25-ft. (7.62 m) PVC SVGA/VGA monitor replacement cable features built-in 3.5mm stereo plugs, for extending audio as well video. The mini-coax (RGB) and paired video wire construction delivers superior video signal quality. Nickel plated connectors and gold plated copper contacts ensure excellent conductivity. Double shielding (foil and braid) provides maximum EMI/RFI protection. Both high density DB15 male connectors are molded and have integral strain relief to ensure they last a long time.

Features

- Extend both Video and Audio signals
- Superior molded cables with foil-shielding for maximum EMI/RFI protection
- Constructed from mini-coax (RGB) and paired video wire construction for superior signal quality.
- HD15 male to HD15 male and 3.5mm to 3.5mm molded connectors
- Computer side Audio Pigtail: 8in Display side Audio Pigtail: 24in
- VW-1 and CM Rated Jacketing

Specifications

| OVERVIEW | |
|--------------------|------------------------------|
| UPC Code | 037332135803 |
| Product Type | Passive |
| Technology | Coax; VGA/SVGA; Stereo Audio |
| PHYSICAL | |
| Color | Black |
| Cable Jacket Color | Black |

| | |
|--------------------------------------|---------------------------|
| Cable Length (ft.) | 25 |
| Cable Length (m) | 7.62 |
| Shipping Dimensions (hwd / in.) | 12.00 x 10.00 x 0.50 |
| Shipping Dimensions (hwd / cm) | 30.48 x 25.40 x 1.27 |
| Shipping Weight (lbs.) | 2.30 |
| Shipping Weight (kg) | 1.04 |
| Unit Dimensions (hwd / in.) | 0.000 x 0.000 x 0.000 |
| CONNECTIONS | |
| Side A - Connector 1 | HD15 (MALE) |
| Side A - Connector 2 | 3.5MM (MALE) |
| Side B - Connector 1 | HD15 (MALE) |
| Side B - Connector 2 | 3.5MM (MALE) |
| Latching or Gripping Connector | No |
| FEATURES & SPECIFICATIONS | |
| IP68 Rated | No |
| WARRANTY & SUPPORT | |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |