

## VGA High-Resolution RGB Coaxial Cable with Audio (HD15 and 3.5mm M/M), 30 ft. (9.14 m)

MODEL NUMBER: P504-030



### Highlights

- Superior molded cables with foil-shielding for maximum EMI/RFI protection
- VW-1 and CM Rated Jacketing
- 3.5mm Stereo Plugs

### Package Includes

30-ft. (9.14 m) SVGA/VGA Monitor Cable HD15M to HD15M w/Built-in Audio connectors

### Description

Tripp Lite's 30-ft. (9.14 m) PVC SVGA/VGA monitor replacement cable features built-in 3.5mm stereo plugs, for extending audio as well video. The mini-coax (RGB) and paired video wire construction delivers superior video signal quality. Nickel plated connectors and gold plated copper contacts ensure excellent conductivity. Double shielding (foil and braid) provides maximum EMI/RFI protection. Both high density DB15 male connectors are molded and have integral strain relief to ensure they last a long time.

### Features

- Extend both Video and Audio signals
- Superior molded cables with foil-shielding for maximum EMI/RFI protection
- Constructed from mini-coax (RGB) and paired video wire construction for superior signal quality.
- HD15 male to HD15 male molded connectors
- Computer side Audio Pigtail: 8in / Display side Audio Pigtail: 24in
- VW-1 and CM Rated Jacketing

## Specifications

OVERVIEW	
UPC Code	037332181237
Technology	Coax; VGA/SVGA; Stereo Audio
Cable Type	Passive
PHYSICAL	
Color	Black
Cable Jacket Color	Black

Cable Length (ft.)	30
Cable Length (m)	9.15
Shipping Dimensions (hwd / in.)	1.00 x 7.50 x 8.30
Shipping Dimensions (hwd / cm)	2.54 x 19.05 x 21.08
Shipping Weight (lbs.)	1.60
Shipping Weight (kg)	0.73
<b>CONNECTIONS</b>	
Side A - Connector 1	HD15 (MALE)
Side A - Connector 2	3.5MM (MALE)
Side B - Connector 1	HD15 (MALE)
Side B - Connector 2	3.5MM (MALE)
Latching or Gripping Connector	No
<b>FEATURES &amp; SPECIFICATIONS</b>	
IP68 Rated	No
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty