



Powering Business Worldwide

Computer Display Cable - 6-ft. VGA Monitor Extension Gold Cable HD15F to HD15M

MODEL NUMBER: P510-006-R



Highlights

- Superior molded cables with foil-shielding for maximum EMI/RFI protection
- Retail packaging

System Requirements

- Monitor with HD15 cable and resolutions up to 640x480.

Package Includes

- 6-ft. VGA Monitor Extension Gold Cable HD15F to HD15M

Description

Tripp Lite's VGA monitor extension cable will extend the reach of a monitor cable by an additional 6ft. Gold plated connectors and gold plated copper contacts ensure excellent conductivity. Shielded for maximum EMI/RFI protection. The HD15 male and HD15 female connectors are molded and have integral strain relief to ensure they last a long time. Tripp Lite warrants this product to be free from defects in materials and workmanship for life. Clamshell retail packaging.

Note: For use with monitors with resolutions up to 640x480 (VGA Std). For higher resolution monitors, please use P500-006.

Features

- Superior molded cables with foil-shielding for maximum EMI/RFI protection
- Gold plated connectors and gold plated copper contacts ensure excellent conductivity
- HD15 male to HD15 female molded connectors

Specifications

OVERVIEW	
UPC Code	037332012333
CONNECTIONS	
Side A - Connector 1	HD15 (MALE)
Side B - Connector 1	HD15 (FEMALE)
Latching or Gripping Connector	No
PHYSICAL	
Cable Length (ft.)	6
Cable Length (m)	1.83



Powering Business Worldwide

Shipping Dimensions (hwd / in.)	0.00 x 0.00 x 0.00
Shipping Weight (lbs.)	0.49
Shipping Weight (kg)	0.22
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.