

## VGA Monitor Extension Cable, 640x480 (HD15 M/F), 25 ft. (7.62 m)

MODEL NUMBER: P510-025



### Description

Tripp Lite's VGA monitor extension cable will extend the reach of a monitor cable by an additional 25-ft. (7.62 m). Gold plated connectors and gold plated copper contacts ensure excellent conductivity. Shielded for maximum EMI/RFI protection. The HD15 male and HD15 female connectors are molded and have integral strain relief to ensure they last a long time. For use with monitors with resolutions up to 640x480 (VGA Std). For higher resolution monitors, please use P500-025.

### Features

- Superior molded cables with foil-shielding for maximum EMI/RFI protection
- Gold plated connectors and gold plated copper contacts ensure excellent conductivity
- HD15 male to HD15 female molded connectors

## Specifications

OVERVIEW	
UPC Code	037332123015
Product Type	Passive Cable
Technology	VGA/SVGA
Cable Type	Passive
PHYSICAL	
Color	Black
Cable Jacket Color	Black
Cable Length (ft.)	25

### Highlights

- Superior molded cables with foil-shielding for maximum EMI/RFI protection

### System Requirements

- Monitor with HD15 cable and resolutions up to 640x480

### Package Includes

- 25-ft. (7.62 m) VGA Monitor Extension Gold Cable HD15F to HD15M

Cable Length (m)	7.62
Cable Length (in.)	300
Shipping Dimensions (hwd / in.)	8.50 x 6.90 x 0.50
Shipping Dimensions (hwd / cm)	21.59 x 17.53 x 1.27
Shipping Weight (lbs.)	0.80
Shipping Weight (kg)	0.36
<b>CONNECTIONS</b>	
Side A - Connector 1	HD15 (MALE)
Side B - Connector 1	HD15 (FEMALE)
Latching or Gripping Connector	No
<b>FEATURES &amp; SPECIFICATIONS</b>	
IP68 Rated	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Compliance	RoHS
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty