

VGA Monitor Cable, 640x480 (HD15 M/M), 10 ft. (3.05 m)

MODEL NUMBER: P512-010



Features

- Superior molded cables with foil-shielding for maximum EMI/RFI protection
- Gold plated connectors and gold plated copper contacts ensure excellent conductivity
- HD15 male to HD15 male molded connectors

Specifications

OVERVIEW	
UPC Code	037332012371
Technology	VGA/SVGA
INPUT	
Cable Length (ft.)	10
Cable Length (m)	3.1
PHYSICAL	
Color	Black
Shipping Dimensions (hwd / cm)	21.59 x 17.53 x 1.27
Shipping Dimensions (hwd / in.)	8.50 x 6.90 x 0.50
Shipping Weight (kg)	0.18
Shipping Weight (lbs.)	0.40

Highlights

- Superior molded cables with foil-shielding for maximum EMI/RFI protection
- For use with monitors with resolutions up to 640x480 (VGA Std). For higher resolution monitors, please use P502-010

System Requirements

- For use with monitors with resolutions up to 640x480 (VGA Std). For higher resolution monitors, please use P502-010

Package Includes

- 10-ft. VGA Monitor Cable
HD15M to HD15M Gold Connectors



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

CONNECTIONS	
Side A - Connector 1	HD15 (MALE)
Side B - Connector 1	HD15 (MALE)
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>