

VGA Monitor Cable, 640x480 (HD15 M/M), 10 ft. (3.05 m)

MODEL NUMBER: **P512-010**



Highlights

- Superior molded cables with foil-shielding for maximum EMI/RFI protection
- For use with monitors with resolutions up to 640x480 (VGA Std). For higher resolution monitors, please use P502-010

System Requirements

- For use with monitors with resolutions up to 640x480 (VGA Std). For higher resolution monitors, please use P502-010

Package Includes

- 10-ft. VGA Monitor Cable
HD15M to HD15M Gold Connectors

Features

- Superior molded cables with foil-shielding for maximum EMI/RFI protection
- Gold plated connectors and gold plated copper contacts ensure excellent conductivity
- HD15 male to HD15 male molded connectors

Specifications

OVERVIEW	
UPC Code	037332012371
Product Type	Passive Cable
Technology	VGA/SVGA
Cable Type	Passive
PHYSICAL	
Color	Black
Cable Jacket Color	Black
Cable Length (ft.)	10
Cable Length (m)	3.05
Cable Length (in.)	120
Shipping Dimensions (hwd / in.)	8.50 x 6.90 x 0.50
Shipping Dimensions (hwd / cm)	21.59 x 17.53 x 1.27

TRIPP-LITE

by **EAT•N**

1000 Eaton Boulevard
Cleveland, OH 44122
United States

Shipping Weight (lbs.)	0.40
Shipping Weight (kg)	0.18
CONNECTIONS	
Side A - Connector 1	HD15 (MALE)
Side B - Connector 1	HD15 (MALE)
Latching or Gripping Connector	No
FEATURES & SPECIFICATIONS	
IP68 Rated	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

TRIPP-LITE

by **EAT•N**

© 2023 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.