

## VGA Monitor Cable, 640x480 (HD15 M/M), 15 ft. (4.57 m)

MODEL NUMBER: P512-015



### Description

Tripp Lite's VGA monitor replacement cable is designed for use with a monitor that has a removable cable with HD15 connectors. This 15-ft. (4.57 m) cable has gold plated connectors and gold plated copper contacts to ensure excellent conductivity. Shielded for maximum EMI/RFI protection. The HD15 male and HD15 female connectors are molded and have integral strain relief to ensure they last a long time. For use with monitors with resolutions up to 640x480 (VGA Std). For higher resolution monitors, please use P502-015.

### Features

- Superior molded cables with foil-shielding for maximum EMI/RFI protection
- Gold plated connectors and gold plated copper contacts ensure excellent conductivity
- HD15 male to HD15 female molded connectors

## Specifications

OVERVIEW	
UPC Code	037332182494
Product Type	Passive Cable
Technology	VGA/SVGA
Cable Type	Passive
PHYSICAL	
Color	Black
Cable Jacket Color	Black
Cable Length (ft.)	15

### Highlights

- Superior molded cables with foil-shielding for maximum EMI/RFI protection

### System Requirements

- Monitor with removable HD15 cable and resolutions up to 640x480.

### Package Includes

- 15-ft. (4.57 m) VGA Monitor Cable HD15M to HD15M Gold Connectors

Cable Length (m)	4.57
Cable Length (in.)	180
Shipping Dimensions (hwd / in.)	0.50 x 5.80 x 6.60
Shipping Dimensions (hwd / cm)	1.27 x 14.73 x 16.76
Shipping Weight (lbs.)	0.50
Shipping Weight (kg)	0.23
<b>CONNECTIONS</b>	
Side A - Connector 1	HD15 (MALE)
Side B - Connector 1	HD15 (MALE)
Latching or Gripping Connector	No
<b>FEATURES &amp; SPECIFICATIONS</b>	
IP68 Rated	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Compliance	RoHS
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty