

## VGA Monitor Y Splitter Cable, High Resolution (HD15 M to 2x HD15 F), 1 ft. (0.31 m)

MODEL NUMBER: P516-001-HR



### Highlights

- Splits the SXGA/UXGA signal providing simultaneous display of the same image on two monitors
- HD15 Male splits to 2 HD15 Female, 1-ft. (0.31 m)

### System Requirements

- PC/MAC with 15-pin Female VGA CPU port

### Package Includes

- 1-ft. (0.31 m) SXGA/UXGA Hi-Res Splitter Cable, HD15M to 2 x HD15F

### Description

This SXGA/UXGA Monitor "Y" Splitter cable provides an inexpensive alternative for splitting the video signal from your PC's VGA port to two high-resolution monitors that use standard 15-pin plugs. 75-ohm coax conductors used for RGBHV signals allow for use with monitors with up to 1600 x 1200 resolutions. Perfect for laptops to display on a separate, larger monitor. Use for short-distance applications only. For applications that require longer distances and highest resolution, see B114-002-R or B114-004-R.

### Features

- HD15 Male to 2 x HD15 Female w/Hex Nuts
- RGB cable construction supports resolutions up to 1600 x 1200
- Molded, double-shielded construction for maximum EMI/RFI protection
- Two monitors display the image from one PC
- Inexpensive solution for presentations

## Specifications

OVERVIEW	
UPC Code	037332142870
Product Type	Splitter
Technology	VGA/SVGA
Host Connector	HD15 (MALE)
Cable Type	Passive
CONNECTIONS	
Side A - Connector 1	HD15 (MALE)
Side B - Connector 1	(2) HD15 (FEMALE)



Powering Business Worldwide



Latching or Gripping Connector	No
Input x Output	1 x 2
Daisy-chainable / Cascadable	No
<b>PHYSICAL</b>	
Color	Black
Cable Jacket Color	Black
Cable Length (ft.)	1
Cable Length (m)	0.30
Cable Length (in.)	12
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Weight (lbs.)	0.30
Shipping Weight (kg)	0.14
<b>FEATURES &amp; SPECIFICATIONS</b>	
MST Support	No
IP68 Rated	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Compliance	RoHS
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.