

## Zero-Skew UTP Bulk Patch Cable for RGB Video, 1000 ft. (304.8 m)

MODEL NUMBER: P524-01K



### Highlights

- High Performance, VGA Video Transmission UTP Bulk Cable
- Riser rated for in wall use
- 1,000ft Bulk Box

### Features

- 24AWG, 4-Pair, Solid Conductor Low Skew Cable, PVC Jacket ( CMR Riser rated, FT4 )
- Skew: 2.2ns/100meters
- Low Skew for minimal distortion and improved signal integrity
- Ideal for VGA over UTP, as well as KVM over Cat5 applications
- Up to 1300-ft distances, depending on equipment manufacturers parameters
- 1,000-ft self-dispensing box

## Specifications

OVERVIEW	
UPC Code	037332147547
Product Type	Passive
PHYSICAL	
Color	Maroon
Cable Length (ft.)	1000
Cable Length (m)	304.8
Shipping Dimensions (hwd / cm)	33.02 x 35.56 x 26.67
Shipping Dimensions (hwd / in.)	13.00 x 14.00 x 10.50
Shipping Weight (kg)	9.07
Shipping Weight (lbs.)	20.00



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

<b>CONNECTIONS</b>	
Side A - Connector 1	BARE WIRE
Side B - Connector 1	BARE WIRE
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>