

DVI Dual Link Cable, Digital TMDS Monitor Cable (DVI-D M/M), 30 ft. (9.14 m)

MODEL NUMBER: P560-030



Description

Tripp Lite's 30-ft. (9.14 m) DVI Dual Link TMDS cable delivers the high performance, high bandwidth needed for today's digital video displays. Gold plated contacts ensure excellent conductivity, while double shielding (foil and braid) provides maximum EMI/RFI protection. Use in conjunction with DVI video cards; a DVI Dual Link video card is required to obtain resolutions up to 2560 x 1600. Both DVI connectors are molded and have integral strain relief for long life reliability.

Features

- DVI-D Dual Link Male-Male, 30-ft. (9.14 m)
- Superior molded cables with foil/braid shielding for maximum EMI/RFI protection
- Gold plated copper contacts ensure excellent conductivity
- Meets DVI DDWG Standard
- Supports 2560 x 1600 resolution
- For use with Digital CRT displays, Flat Panel Displays, HDTV and Projectors

Specifications

OVERVIEW	
UPC Code	037332185983
Technology	DVI
Cable Type	Passive
PHYSICAL	
Color	Black
Cable Jacket Color	Black

Highlights

- DVI-D Dual Link TMDS Male-Male, 30-ft. (9.14 m)
- Compatible with Flat Panel Displays, Digital CRT Displays and Projectors
- Provides bandwidth for resolutions up to 2560 x 1600
- High Speed Digital Transmission to 9.9Gbps
- Superior molded cables with foil/braid shielding for maximum EMI/RFI protection

System Requirements

- Monitor with DVI, and CPU with a DVI video card. Video card must support Dual Link in order to obtain resolutions up to 2560 x 1600

Package Includes

- DVI Dual Link TMDS cable - DVI-D, M/M, 30-ft. (9.14 m)

Cable Length (ft.)	30
Cable Length (m)	9.15
Shipping Dimensions (hwd / in.)	12.00 x 10.00 x 0.50
Shipping Dimensions (hwd / cm)	30.48 x 25.40 x 1.27
Shipping Weight (lbs.)	1.96
Shipping Weight (kg)	0.89
Unit Dimensions (hwd / in.)	0.000 x 0.000 x 0.000
CONNECTIONS	
Side A - Connector 1	DVI-D DUAL LINK (MALE)
Side B - Connector 1	DVI-D DUAL LINK (MALE)
Latching or Gripping Connector	No
FEATURES & SPECIFICATIONS	
IP68 Rated	No
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty