

In most applications, a signal booster (Model Number: B120-000) will need to be used with this cable to ensure a signal strong enough for your display.

DVI High Definition Dual Link Digital TMDS Monitor Cable (DVI-D M/M), 100 ft. (30.5 m)

MODEL NUMBER: P560-100-HD



Highlights

- 24AWG High Definition Cable
- For use with Dual TMDS Link specified video cards
- Compatible with Flat Panel Displays, Digital CRT Displays and Projectors
- Provides bandwidth for resolutions up to 2560 x 1600
- High Speed Digital Transmission to 9.9Gbps
- Superior molded cables with foil/braid shielding for maximum EMI/RFI protection

System Requirements

- DVI monitor and computer

Package Includes

- 100-ft. (30.5 m) DVI High Definition Dual Link TMDS Cable (DVI-D M/M)

Description

Tripp Lite's 100-ft. (30.5 m), High Definition DVI Dual Link TMDS cable delivers the high performance and high bandwidth needed for today's digital video displays. 24AWG wire and gold-plated contacts ensure excellent conductivity, while double shielding (foil and braid) provides maximum EMI/RFI protection. Use in conjunction with DVI video cards that are specified as Dual Link. Both DVI connectors are molded, have integral strain relief for long life reliability, and ferrite collars to drain off extraneous electrical interference. In most applications, a signal booster (B120-000) will need to be used with this cable to ensure a signal strong enough for your display.

Features

- 24AWG High Definition Cable
- Superior molded cables with foil/braid shielding for maximum EMI/RFI protection
- Dual Link digital signalling for transmission speeds to 9.9Gbps
- Meets DVI DDWG Standard
- PC and Mac compatible
- For use with Digital CRT displays, Flat Panel Displays, HDTV and Projector
- In most applications, a signal booster (B120-000) will need to be used with this cable to ensure a signal strong enough for your display.

Specifications

OVERVIEW	
UPC Code	037332177872



Product Type	Passive
Technology	DVI
PHYSICAL	
Color	Black
Cable Length (ft.)	100
Cable Length (m)	30.5
Shipping Dimensions (hwd / cm)	12.70 x 27.18 x 38.10
Shipping Dimensions (hwd / in.)	5.00 x 10.70 x 15.00
Shipping Weight (kg)	4.31
Shipping Weight (lbs.)	9.50
CONNECTIONS	
Side A - Connector 1	DVI-D DUAL LINK (MALE)
Side B - Connector 1	DVI-D DUAL LINK (MALE)
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>