

## DVI Single Link Cable, Digital and Analog TMDS Monitor Cable (DVI-I M/M), 6 ft. (1.83 m)

MODEL NUMBER: P561-006-SLI



### Features

- DVI-I transmits both digital and analog video signals. Can be converted for use with a VGA monitor using a Tripp Lite P126-000 adapter
- Superior molded cables with foil/braid shielding for maximum EMI/RFI protection
- Gold plated contacts ensure excellent conductivity
- Compatible with Flat Panel Displays, Digital CRT Displays and Projectors
- Supports DVI Single Link computer video resolutions up to 1920 x 1200, and HD resolutions up to 1920 x 1080
- Supports high speed data transmission rates up to 4.95Gbps
- PC and Mac compatible
- Meets DVI DDWG standards

### Highlights

- DVI-I transmits both digital and analog video signals. Can be converted for use with a VGA monitor using a Tripp Lite P126-000 adapter
- Superior molded cables with foil/braid shielding for maximum EMI/RFI protection
- Gold plated contacts ensure excellent conductivity
- Compatible with Flat Panel Displays, Digital CRT Displays and Projectors
- Supports DVI Single Link computer video resolutions up to 1920 x 1200, and HD resolutions up to 1920 x 1080
- Supports high speed data transmission rates up to 4.95Gbps
- Meets DVI DDWG standards

### System Requirements

- DVI computer and monitor with DVI-I ports
- Can be converted for use with VGA monitors and/or computers using a Tripp Lite P126-000 adapter
- In order to transmit from a DVI computer to a VGA monitor, the computer must support DVI-I Digital/Analog data transmission

### Package Includes

- P561-006-SLI DVI-I Single Link Digital/Analog Monitor Cable



## Specifications

OVERVIEW	
UPC Code	037332181510
Product Type	Passive
Technology	DVI
PHYSICAL	
Color	Black
Cable Length (ft.)	6
Cable Length (m)	1.8
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.02
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.40
Shipping Weight (kg)	0.27
Shipping Weight (lbs.)	0.60
CONNECTIONS	
Side A - Connector 1	DVI-I SINGLE LINK (MALE)
Side B - Connector 1	DVI-I SINGLE LINK (MALE)
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>