

HDMI to DisplayPort Active Adapter Cable (M/M) - 4K 60 Hz, USB Power, Black, 1 m (3.3 ft.)

MODEL NUMBER: P567-01M-4K6



Connects a DisplayPort monitor, HDTV or projector to the HDMI port on your Blu-ray player, computer, media server or other AV source.

Features

Active Adapter Cable Connects a 4K Monitor to Your Computer or Media Server

This all-in-one video converter cable (M/M) lets you transmit 4K video with digital audio from the HDMI port on your Blu-ray player, satellite/cable box, computer or media server to your 4K DisplayPort-enabled monitor, projector or television. It's recommended for home theater systems, digital signage, trade show displays and conference room presentations. You can continue using your existing DisplayPort monitor without the expense of a new HDMI display to match your source device.

Transmits 4K Video with 4:4:4 Color

The P567-01M-4K6 supports Ultra HD 4K resolutions up to 4096 x 2160 at 60 Hz with 7.1-channel surround sound, 36-bit Deep Color and HDCP 1.4 encryption for streaming 4K content with no loss in resolution. This cable also supports uncompressed 4:4:4 chroma subsampling for top-level PC gaming or using your HDTV as a PC monitor.

Ready to Use Right from the Package, So You Can Plug and Play Immediately

The plug-and-play cable requires no drivers or external power. The bus-powered cable receives any necessary extra power from the source device via the included USB-A connector. It is compatible with all HDMI sources and all major operating systems, including Windows, macOS and Linux. It is backward compatible with 1080p displays, so you can use the cable with older equipment.

Specifications

OVERVIEW	
UPC Code	037332296474
Product Type	Active Cable
Technology	HDMI; DisplayPort
Cable Type	Active

Highlights

- Supports UHD resolutions up to 4K @ 60 Hz (4:4:4) for heightened video quality
- Ideal for lectures, presentations, trade shows, digital signage and home theaters
- Bus-powered through USB connection to source; USB-A connector included
- Works with all HDMI sources and all major operating systems, including Windows
- Plug-and-play operation with no software required for easy, immediate installation

System Requirements

- Source device with HDMI output (Blu-ray player, computer, media server, etc.)
- Display device with DisplayPort input (monitor, television, projector, etc.)

Package Includes

- P567-01M-4K6 HDMI 1.4 to DisplayPort 1.2 Active Adapter Cable, Black, 1 m (3.3 ft.)
- Installation instructions



Powering Business Worldwide

TRIPP LITE
SERIES

VIDEO	
Max Supported Video Resolution	4096 x 2160 (4K X 2K) @ 60Hz
Max Supported Color Depth	36-bit Deep Color
HDR Support	No
3D Video Supported	No
Chroma Sub Sampling	4:4:4
Maximum Signal Range (ft)	3.3
Maximum Signal Range (m)	1
DisplayPort Alt Mode	No
AUDIO	
Audio Specification	7.1 CHANNEL SURROUND SOUND
INPUT	
Bus Powered	Yes
CONNECTIONS	
Side A - Connector 1	HDMI (MALE)
Side B - Connector 1	DISPLAYPORT (MALE); USB A (MALE)
Connector Plating	Nickel
Contact Plating	Gold
Connector Style	Straight
Latching or Gripping Connector	Yes
PHYSICAL	
Color	Black
Material of Construction	PVC + ABS
Cable Jacket Color	Black
Connector Color	Black
Cable Jacket Material	PVC
Cable Jacket Rating	VW-1
Cable Outer Diameter (OD)	3.0MM
Wire Gauge (AWG)	24
Wire Gauge (OD - mm ²)	24
Cable Length (ft.)	3.3
Cable Length (m)	1.01
Cable Length (in.)	39.4



Powering Business Worldwide

TRIPP LITE
SERIES

Shipping Dimensions (hwd / in.)	0.91 x 6.50 x 5.32
Shipping Weight (kg)	0.07
Unit Dimensions (hwd / in.)	0.910 x 6.500 x 5.320
Unit Packaging Type	Box
Unit Weight (lbs.)	0.14
Unit Weight (kg)	0.06
ENVIRONMENTAL	
Operating Temperature Range	32° to 158°F (0° to 70°C)
Storage Temperature Range	14° to 176°F (-10° to 80°C)
Operating Humidity Range	10% to 85% RH, Non-Condensing
Storage Humidity Range	5% to 90% RH, Non-Condensing
Power Provided to Connected Device(s)	USB-A: 5V/0.5A (2.5W)
COMMUNICATIONS	
Signal Range (ft.)	3.3
Signal Range (m)	1
EDID Compatible	Yes
Consumer Electronics Control (CEC) Supported	No
FEATURES & SPECIFICATIONS	
EMI/RFI Line Noise Protection	Yes
Integrated/Removable Cable	No
MST Support	No
Antibacterial	No
IP68 Rated	No
IP20 Rated	No
Fully Molded Connector Ends	No
Ohms	No
Integral Strain Relief	No
Impedance-Matched Twisted-Pair Construction	No
Scaler Function	No
IP67 Rated	No
Armored Cable	No
Displayport Specification	1.2
HDCP Specification	1.4



Powering Business Worldwide

TRIPP LITE
SERIES

Driver Required	No
DIN Mountable	No
STANDARDS & COMPLIANCE	
Product Certifications	EN 55032; EN 55035
Product Compliance	CE (Europe); FCC (USA); REACH; RoHS; UKCA; WEEE
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.