

HDMI to DisplayPort Active Adapter Cable (M/M) - 4K, USB Power, Black, 2 m (6.6 ft.)

MODEL NUMBER: **P567-02M**



Connects a DisplayPort monitor or projector to the HDMI port on your Blu-ray player, computer, media server or other A/V source.

Features

Active Adapter Cable Connects a 4K Monitor to Your Computer or Media Server

This all-in-one video converter cable lets you transmit 4K video with digital audio from the HDMI port on your Blu-ray player, satellite/cable box, computer or media server to your 4K DisplayPort-enabled monitor, projector or television. It's recommended for home theater systems, digital signage, trade show displays and conference room presentations. You can continue using your existing DisplayPort monitor without the expense of a new HDMI display to match your source device.

Transmits Crystal-Clear True 4K Video with Audio and 4:4:4 Color

The P567-02M supports Ultra HD video resolutions up to 4096 x 2160 (4K x 2K) at 30 Hz with rich, full 7.1-channel surround sound, 36-bit Deep Color, HDCP 1.4 and 4:4:4 chroma subsampling for top-level PC gaming or using your HDTV as a PC monitor. Additionally, this cable transmits EDID information to ensure optimal display compatibility.

Ready to Use Right from the Package, So You Can Plug and Play Immediately

The plug-and-play cable requires no drivers or external power. The bus-powered cable receives any necessary extra power from the source device via the included USB-A connector. It is compatible with all HDMI sources and all major operating systems, including Windows, macOS and Linux. It is backward compatible with 1080p displays, so you can use the cable with older equipment.

Specifications

| OVERVIEW | |
|------------|-------------------|
| UPC Code | 037332261274 |
| Technology | DisplayPort; HDMI |
| VIDEO | |

Highlights

- Supports UHD resolutions up to true 4K @ 30 Hz (4:4:4) for crystal-clear video
- Ideal for lectures, presentations, trade shows, digital signage and home theaters
- Bus-powered through USB connection to source; USB-A connector included
- Works with all HDMI sources and all major operating systems, including Windows
- Plug-and-play operation with no software required for easy, immediate installation

Applications

- Stream 4K movies and other programming from a Blu-ray player, game system or cable box to an HDTV
- Add a second monitor to your PC for multitasking purposes or editing video
- Upgrade the video quality of your digital signage to true 4K

System Requirements

- Source device with HDMI output (Blu-ray player, computer, media server, etc.)
- Display device with DisplayPort input (monitor, television, projector, etc.)

Package Includes

- P567-02M HDMI to DisplayPort 1.2 Active Adapter Cable, Black, 2 m (6.6 ft.)
- Owner's manual

| | |
|---------------------------------------|----------------------------------|
| Max Supported Video Resolution | 4096 x 2160 (4K x 2K) @ 30Hz |
| Max Supported Color Depth | 36-bit Deep Color |
| HDR Support | No |
| Chroma Sub Sampling | 4:4:4 |
| AUDIO | |
| Audio Specification | 7.1 Channel Surround Sound |
| INPUT | |
| Bus Powered | Yes |
| PHYSICAL | |
| Color | Black |
| Cable Jacket Color | Black |
| Cable Jacket Material | PVC |
| Cable Jacket Rating | VW-1 |
| Cable Outer Diameter (OD) | 6.0mm |
| Wire Gauge (AWG) | 30 |
| Cable Length (ft.) | 6.6 |
| Cable Length (m) | 2.01 |
| Cable Length (in.) | 78.7 |
| ENVIRONMENTAL | |
| Operating Temperature Range | 32 to 158 F (0 to 70 C) |
| Storage Temperature Range | 14 to 176 F (-10 to 80 C) |
| Operating Humidity Range | 10% to 85% RH, Non-Condensing |
| Storage Humidity Range | 5% to 90% RH, Non-Condensing |
| Power Provided to Connected Device(s) | USB-A: 5V/0.5A (2.5W) |
| COMMUNICATIONS | |
| EDID Compatible | Yes |
| CONNECTIONS | |
| Side A - Connector 1 | HDMI (MALE) |
| Side B - Connector 1 | DISPLAYPORT (MALE); USB A (MALE) |
| Connector Plating | Gold |
| Contact Plating | Gold |

| FEATURES & SPECIFICATIONS | |
|-------------------------------------|-------------------------------------|
| Displayport Specification | 1.2 |
| HDCP Specification | 1.4 |
| Driver Required | No |
| Fully Molded Connector Ends | No |
| EMI/RFI Line Noise Protection | Yes |
| IP68 Rated | No |
| IP20 Rated | No |
| STANDARDS & COMPLIANCE | |
| Product Compliance | RoHS; CE (Europe); REACH; FCC (USA) |
| WARRANTY & SUPPORT | |
| Product Warranty Period (Worldwide) | 2-year limited warranty |