

## High-Speed HDMI Cable (M/M) - 4K, Gripping Connectors, White, 3 ft. (0.9 m)

MODEL NUMBER: P568-003-WH



Connects two 4K-enabled devices, including computers, Blu-ray players, video game systems, DVRs, video cameras, A/V receivers, monitors, projectors and televisions.

### Description

The P568-003-WH High-Speed HDMI 4K Cable (M/M) is recommended for digital signage, video presentations, point-of-sale displays, classrooms and other applications that display Ultra High Resolution (UHD) video and multi-channel audio. It connects 4K-enabled source devices, such as computers and Blu-ray players, to 4K-enabled displays, such as monitors, projectors and televisions.

This cable supports video resolutions up to Ultra HD 4K x 2K (4096 x 2160) at 30 Hz. When used with an Apple digital AV adapter, it supports iPad2 video mirroring for playing games, watching videos or displaying presentations.

The three-foot (0.9-meter) molded 30 AWG cable features premium foil and braid shielding to deliver reliable, error-free signal quality and protection from EMI/RFI line noise that can distort or destroy data. Gold-plated white connectors provide maximum conductivity and minimize data loss. Integral strain relief gives the cable extra flexibility, reduces stress, and helps the cable and connectors move freely without cracking. A flexible PVC jacket makes the HDCP pass-through cable easy to install in tight spaces.

### Features

**Connects HDMI Source to 4K TV, Projector or Monitor** Ideal for digital signage, video presentations, point-of-sale displays, classrooms and other applications with 4K video and multi-channel audio

**High Performance and Wide Compatibility** Supports UHD video resolutions up to 4K Complies with HDCP pass-through standards Supports iPad2 video mirroring when used with Apple digital A/V adapter Backward compatible with previous HDMI generations

**Superior Quality Ensures a Flawless Signal** Corrosion-resistant gold-plated white connectors for maximum conductivity and minimum data loss Fully molded 30 AWG construction with integral strain relief reduces stress and adds flexibility Premium foil and braid shielding for EMI/RFI noise protection Flexible PVC jacket easy to install in tight spaces

### Highlights

- Supports UHD video resolutions up to 4K
- Backward compatible with previous HDMI generations
- Premium foil and braid shielding protects against EMI/RFI noise
- Gold-plated white connectors for optimal signal transfer

### Package Includes

P568-003-WH High-Speed HDMI Cable (M/M), White, 3 ft. (0.9 m)

## Specifications

### OVERVIEW

UPC Code

037332184795



Powering Business Worldwide

TRIPP LITE  
SERIES

|  |                         |
|--|-------------------------|
| Product Type                                 | Passive Cable           |
| Technology                                   | HDMI                    |
| Cable Type                                   | Passive                 |
| <b>VIDEO</b>                                 |                         |
| Max Supported Video Resolution               | 3840 x 2160 (4K) @ 30Hz |
| Max Supported Color Depth                    | 24-bit True Color       |
| HDR Support                                  | No                      |
| 3D Video Supported                           | No                      |
| Chroma Sub Sampling                          | 4:4:4                   |
| EDID Support                                 | Yes                     |
| Signal Transmission                          | Bidirectional           |
| <b>AUDIO</b>                                 |                         |
| Audio Specification                          | Stereo Audio            |
| <b>CONNECTIONS</b>                           |                         |
| Side A - Connector 1                         | HDMI (MALE)             |
| Side B - Connector 1                         | HDMI (MALE)             |
| Connector Plating                            | Gold                    |
| Contact Plating                              | Gold                    |
| Connector Style                              | Straight                |
| Latching or Gripping Connector               | No                      |
| <b>USER INTERFACE, ALERTS &amp; CONTROLS</b> |                         |
| LED Indicators                               | 0                       |
| <b>PHYSICAL</b>                              |                         |
| Color  | White                   |
| Cable Jacket Color                           | White                   |
| Connector Color                              | White                   |
| Cable Jacket Material                        | PVC                     |
| Cable Jacket Rating                          | VW-1                    |
| Cable Outer Diameter (OD)                    | 5.5 mm                  |
| Wire Gauge (AWG)                             | 30                      |
| Cable Length (ft.)                           | 3                       |
| Cable Length (m)                             | 0.91                    |
| Cable Length (in.)                           | 36                      |



Powering Business Worldwide

TRIPP LITE  
SERIES

|  |                               |
|--|-------------------------------|
| Ferrite Core                                 | No                            |
| Minimum Bend Radius                          | 55mm                          |
| Shipping Dimensions (hwd / in.)              | 9.00 x 7.00 x 0.50            |
| Shipping Dimensions (hwd / cm)               | 22.86 x 17.78 x 1.27          |
| Shipping Weight (lbs.)                       | 0.18                          |
| Shipping Weight (kg)                         | 0.08                          |
| <b>ENVIRONMENTAL</b>                         |                               |
| Operating Temperature Range                  | 32° to 113°F (0° to 45°C)     |
| Storage Temperature Range                    | -40° to 176°F (-40° to 80°C)  |
| Operating Humidity Range                     | 10% to 85% RH, Non-Condensing |
| Storage Humidity Range                       | 5% to 90% RH, Non-Condensing  |
| <b>COMMUNICATIONS</b>                        |                               |
| Consumer Electronics Control (CEC) Supported | Yes                           |
| <b>FEATURES &amp; SPECIFICATIONS</b>         |                               |
| EMI/RFI Line Noise Protection                | No                            |
| MST Support                                  | No                            |
| Antibacterial                                | No                            |
| IP68 Rated                                   | No                            |
| IP20 Rated                                   | No                            |
| Armored Cable                                | No                            |
| Ethernet Support                             | No                            |
| HDCP Specification                           | 1.3                           |
| <b>STANDARDS &amp; COMPLIANCE</b>            |                               |
| Product Compliance                           | RoHS; REACH                   |
| <b>WARRANTY &amp; SUPPORT</b>                |                               |
| Product Warranty Period (Worldwide)          | Lifetime limited warranty     |

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.