

In most applications where the HDMI cable exceeds 16ft, a signal booster (B122-000-60) will need to be used with this cable to ensure a signal strong enough for your display

High-Speed HDMI Easy Pull Cable, Digital Video with Audio (M/M), 25 ft.

MODEL NUMBER: **P568-025-EZ**



Description

Tripp Lite's 25 ft. High Speed HDMI Easy Pull Monitor Cable w/ Connectors makes running long length video cables a snap. The pull-apart design allows the cable to be run through conduit or other tight areas that a HDMI connector wouldn't fit through. Diameter of the circular DIN end is only 7/8". Circular Easy Pull connector is threaded to ensure maximum security once the cable is reattached. Double shielding (foil and braid) provides maximum EMI/RFI protection. Both HDMI male ends are molded and have integral strain relief to provide long life. UL20276 Digital Video Cable supports 1080p. In most applications, a signal booster (B122-000-60) will need to be used with this cable to ensure a signal strong enough for your display.

Features

- Two-piece design runs through conduit or other tight areas
- Threaded circular DIN connector provides secure reattachment
- Superior-molded cables with foil and braid shielding for maximum EMI/RFI protection
- High quality quad-shielded cable with Gold connectors and pins
- Bandwidth up to 10.2 Gbps - Full 1080p resolution as specified by HDMI 1.2
- High Speed HDMI and HDCP compliant
- In most applications where the HDMI cable exceeds 16ft, a signal booster (B122-000-60) will need to be used with this cable to ensure a signal strong enough for your display
- HDMI male to male molded connectors
- UL20276 Digital Video Cable
- Supports High Definition (HD) video resolutions up to 1080p

Specifications

Highlights

- Two-piece design runs through conduit or other tight areas
- Threaded circular DIN connector provides secure reattachment
- Superior-molded cables with foil and braid shielding for maximum EMI/RFI protection
- Bandwidth up to 10.2 Gbps - Full 1080p resolution as specified by HDMI 1.2
- High Speed HDMI and HDCP compliant
- Supports High Definition (HD) video resolutions up to 1080p

Package Includes

- High Speed HDMI Easy Pull Cable, HD 1080p, Digital Video with Audio (M/M), 25-ft.



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

OVERVIEW	
UPC Code	037332175564
INPUT	
Cable Length (ft.)	25
Cable Length (m)	7.6
PHYSICAL	
Color	Black
Shipping Dimensions (hwd / cm)	2.54 x 17.53 x 22.35
Shipping Dimensions (hwd / in.)	1.00 x 6.90 x 8.80
Shipping Weight (kg)	0.41
Shipping Weight (lbs.)	0.90
Wire Gauge (AWG)	28
CONNECTIONS	
Side A - Connector 1	HDMI (MALE)
Side B - Connector 1	HDMI (MALE)
FEATURES & SPECIFICATIONS	
Max Supported Video Resolution	1920 x 1080 @60Hz
HDMI Specification	1.2
Technology	HDMI
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>