

High-Speed HDMI Cable with Ethernet, Digital Video with Audio (M/F), Panel Mount, 3 ft. (0.91 m)

MODEL NUMBER: **P569-003-MF-APM**



Highlights

- Male end connects high-definition equipment
- Panel-mount female end attaches with included hardware
- Corrosion-resistant gold-plated molded connectors
- Shielded 28 AWG wire
- Flexible PVC jacket with integral strain relief

Package Includes

- P569-003-MF-APM High-Speed HDMI Panel-Mount Cable (M/F), 3 ft.
- Mounting hardware

High-speed HDMI cable with panel-mounted female connector extends your HDMI signal and provides a female panel-mount connection for use in a trade show booth, retail kiosk, podium, or the front panel of a computer. Ideal for digital signage, home theater, professional audio/video and data center applications.

Features

Adds a Panel-Mounted HDMI Port

- Extends HDMI interface in a digital signage, home theater, professional audio/video or data center application
- Female end mounts to a trade show booth, retail kiosk, teacher's or lecturer's podium or the front panel of a computer

Premium Construction for Premium Performance

- Corrosion-resistant gold-plated connectors for optimal signal transfer
- Fully molded construction with integral strain relief for durability and long life
- Flexible PVC jacket easy to install in tight spaces
- Shielded 28 AWG wire

Specifications

OVERVIEW	
UPC Code	037332191755
Technology	HDMI
PHYSICAL	
Color	Black

Cable Jacket Color	Black
Cable Length (ft.)	3
Cable Length (m)	0.91
Cable Length (in.)	36
Cable Length (cm)	91.44
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Weight (lbs.)	0.17
Shipping Weight (kg)	0.08
Unit Dimensions (hwd / in.)	9.000 x 7.000 x 0.500
CONNECTIONS	
Side A - Connector 1	HDMI (FEMALE) - PANEL MOUNT
Side B - Connector 1	HDMI (MALE)
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty