


## High Speed HDMI Cable with Ethernet, UHD 4K, Digital Video with Audio (M/M), 10 ft. (3.05 m)

MODEL NUMBER: P569-010



### Highlights

- 10-ft. (3.05 m) High Speed with Ethernet HDMI cable v1.4
- Supports transmission speeds up to 18 Gbps
- Backward compatible to previous HDMI generations
- Video mirroring with iPad2

### System Requirements

- HDMI video source and HDMI enabled TV / Monitor

### Package Includes

- 10-ft. (3.05 m) High Speed with Ethernet HDMI Cable v1.4

### Features

- 10-ft. (3.05 m) High Speed with Ethernet HDMI cable v1.4
- Supports transmission speeds up to 18 Gbps
- Backward compatible to previous HDMI generations
- Fully molded cables, with Gold plated connectors assures long life
- Perfect for connecting an iPad2 to an HDTV (video mirroring) to watch movies, play games, surf the web and display presentations

## Specifications

OVERVIEW	
UPC Code	037332160690
Product Type	Passive
Technology	HDMI
VIDEO	
Max Supported Video Resolution	3840 x 2160 @ 30Hz
Max Supported Color Depth	24-bit True Color
HDR Support	No
3D Video Supported	Yes
Chroma Sub Sampling	4:4:4
EDID Support	Yes



Signal Transmission	Bidirectional
<b>AUDIO</b>	
Audio Specification	Stereo Audio
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
LED Indicators	0
<b>PHYSICAL</b>	
Color	Black
Cable Jacket Color	Black
Connector Color	Black
Cable Jacket Material	PVC
Cable Jacket Rating	VW-1
Cable Outer Diameter (OD)	6mm
Wire Gauge (AWG)	28
Cable Length (ft.)	10
Cable Length (m)	3.05
Ferrite Core	No
Minimum Bend Radius	60mm
Shipping Dimensions (hwd / cm)	17.78 x 22.86 x 1.27
Shipping Dimensions (hwd / in.)	7.00 x 9.00 x 0.50
Shipping Weight (kg)	0.16
Shipping Weight (lbs.)	0.35
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	32 TO 113 F (0 TO 45 C)
Storage Temperature Range	-40 - 80 °C (-40 - 176 °F)
Operating Humidity Range	10 to 85% RH, Non-Condensing
Storage Humidity Range	5 to 90% RH, Non-Condensing
<b>COMMUNICATIONS</b>	
Consumer Electronics Control (CEC) Supported	Yes
<b>CONNECTIONS</b>	
Side A - Connector 1	HDMI (MALE)
Side B - Connector 1	HDMI (MALE)



Connector Plating	Gold
Contact Plating	Gold
Connector Style	Straight
Latching or Gripping Connector	No
<b>FEATURES &amp; SPECIFICATIONS</b>	
HDCP Specification	1.4
EMI/RFI Line Noise Protection	No
MST Support	No
IP68 Rated	No
Antibacterial	No
Armored Cable	No
Ethernet Support	Yes
IP20 Rated	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Compliance	RoHS; REACH
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2022 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>