

High-Speed HDMI Cable with Ethernet (M/M) - UHD 4K, In-Wall CL3-Rated, 16 ft.

MODEL NUMBER: P569-016-CL3



Transmits digital audio/video and Ethernet signals from an HDMI source to a 4K television, projector or monitor. Ideal for in-wall home theater systems, digital signage and other applications that display UHD video.

Description

The P569-016-CL3 High-Speed HDMI Cable (M/M) is ideal for home theater systems, digital signage and other applications that display Ultra High Resolution (UHD) video and multi-channel audio. It connects an HDMI-enabled source device, such as a Blu-ray player, video game system or computer, to a 4K-enabled television, monitor or projector.

The P569-016-CL3 carries a CL3 rating, making it suitable for in-wall installation. It supports UHD video resolutions up to 3840 x 2160 (4K x 2K), data transfer speeds up to 18 Gbps and 3D. It works in all HDMI cabling scenarios.

This HDMI cable supports Ethernet data connectivity, which allows web-capable devices to share their internet connection with other connected HDMI devices. An audio return channel simplifies setups between displays and A/V receivers. When used with an Apple digital A/V adapter, it supports iPad2 video mirroring for playing games, watching videos or displaying presentations.

The 16-foot (4.9-meter) molded 30 AWG cable features premium foil and braid shielding to deliver top-of-the-line signal quality and protection from EMI/RFI interference. Gold-plated connectors ensure excellent conductivity. Integral strain relief ensures the cable and connectors last a long time. A flexible CL3-rated PVC jacket makes the cable easy to install in tight spaces.

Features

Connects HDMI Source to 4K TV, Projector or Monitor

- Ideal for home theater systems, digital signage and other applications that display UHD video and multi-channel audio
- CL3 rating suitable for in-wall installation

High Performance and Wide Compatibility

- Supports UHD and 3D video resolutions up to 3840 x 2160 (4K x 2K)
- Supports data transfer speeds up to 18 Gbps

Highlights

- Supports UHD and 3D video resolutions up to 3840 x 2160 (4K x 2K)
- Supports data transfer speeds up to 18 Gbps
- Premium foil and braid shielding protects against EMI/RFI noise
- CL3-rated jacket supports in-wall installation

Package Includes

P569-016-CL3 High-Speed HDMI Cable with Ethernet (M/M), 16 ft.



- Supports iPad2 video mirroring when used with Apple digital A/V adapter
- Works in all HDMI cabling scenarios

Superior Quality Ensures a Flawless Signal

- Fully molded 30 AWG construction with integral strain relief for durability and long life
- Premium foil and braid shielding for EMI/RFI noise protection
- Corrosion-resistant gold-plated connectors for optimal signal transfer
- Flexible PVC jacket easy to install in tight spaces

Specifications

OVERVIEW	
UPC Code	037332197351
Product Type	Passive
Technology	HDMI
PHYSICAL	
Color	Black
Cable Length (ft.)	16
Cable Length (m)	4.9
Shipping Dimensions (hwd / cm)	23.01 x 17.98 x 1.27
Shipping Dimensions (hwd / in.)	9.06 x 7.08 x 0.50
Shipping Weight (kg)	0.34
Shipping Weight (lbs.)	0.75
CONNECTIONS	
Side A - Connector 1	HDMI (MALE)
Side B - Connector 1	HDMI (MALE)
SPECIAL FEATURES	
Fire Rating	CL3 Rated
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>