

HDMI to Micro HDMI Cable with Ethernet, Digital Video with Audio Adapter (M/M), 3 ft. (0.91 m)

MODEL NUMBER: P570-003-MICRO



Highlights

- 3-ft. (0.91 m) HDMI to Micro HDMI High Speed w/Ethernet Cable
- Micro HDMI connector is 50% smaller than standard HDMI
- Complies with HDMI v1.4 Type D connections
- Full 1080p, 3D, Blu-Ray, Ethernet, Digital Audio transfer

System Requirements

- Device with Micro-HDMI output, to Display with standard HDMI Input

Package Includes

- 3-ft. (0.91 m) HDMI to Micro HDMI High Speed w/Ethernet Audio/Video Cable

Description

This HDMI to Micro HDMI High Speed w/Ethernet Audio/Video cable allow devices with Micro-HDMI output ports, such as smartphones and other portable devices, to attach to standard HDMI displays, such as HDTVs, monitors and projectors. Cable complies with HDMI v1.4 specifications and is capable of transferring 1080p, Ethernet, 3D video, as well as digital audio.

Featuring a full 19-pin array like larger HDMI connectors, only in a miniaturized version, the HDMI Micro Connector saves space on portable devices, while allowing the full capabilities of current HDMI v1.4 digital signaling.

Features

- 3-ft. (0.91 m) HDMI to Micro HDMI High Speed w/Ethernet Cable
- Compliant with HDMI v1.4 specifications, Type D Connector
- 1080p, 3D, Blu-Ray, Ethernet, Digital Audio transfer
- Mylar Foil and Braid Shielding for maximum noise suppression
- Rugged, molded connectors for a lifetime of use
- Gold plated contacts and connector shell assures highest signal quality

Specifications

OVERVIEW	
UPC Code	037332165473
Product Type	Passive Cable
Technology	HDMI
Cable Type	Passive
VIDEO	
Max Supported Video Resolution	1920 x 1200 (1080p)



Powering Business Worldwide

TRIPP LITE
SERIES

Max Supported Color Depth	48-bit Deep Color
HDR Support	No
3D Video Supported	Yes
Chroma Sub Sampling	4:4:4
EDID Support	Yes
Signal Transmission	Bidirectional
AUDIO	
Audio Specification	ARC
CONNECTIONS	
Side A - Connector 1	MICRO HDMI (MALE)
Side B - Connector 1	HDMI (MALE)
Connector Plating	Gold
Contact Plating	Gold
Connector Style	Straight
Latching or Gripping Connector	No
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	0
PHYSICAL	
Color	Black
Material of Construction	PVC
Cable Jacket Color	Black
Connector Color	Black
Cable Jacket Material	PVC
Cable Jacket Rating	VW-1
Cable Outer Diameter (OD)	4.5 mm
Wire Gauge (AWG)	34
Cable Length (ft.)	3
Cable Length (m)	0.91
Cable Length (in.)	36
Ferrite Core	No
Minimum Bend Radius	22.5mm
Shipping Dimensions (hwd / in.)	0.25 x 4.70 x 9.10
Shipping Dimensions (hwd / cm)	0.64 x 11.94 x 23.11



Powering Business Worldwide

TRIPP LITE
SERIES

Shipping Weight (lbs.)	0.20
Shipping Weight (kg)	0.09
ENVIRONMENTAL	
Operating Temperature Range	14° to 122°F (-10° to 50°C)
Storage Temperature Range	5° to 140°F (-15° to 60°C)
Operating Humidity Range	0% to 90% RH, Non-Condensing
Storage Humidity Range	0% to 90% RH, Non-Condensing
COMMUNICATIONS	
EDID Compatible	Yes
Consumer Electronics Control (CEC) Supported	Yes
FEATURES & SPECIFICATIONS	
EMI/RFI Line Noise Protection	No
MST Support	No
Antibacterial	No
IP68 Rated	No
IP20 Rated	No
Armored Cable	No
Ethernet Support	Yes
HDCP Specification	1.4; 2.2
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; REACH
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.