

High-Speed HDMI to Mini HDMI Cable with Ethernet, Digital Video with Audio Adapter (M/M), 1 ft.

MODEL NUMBER: **P571-001-MINI**



High-speed cable connects a mini-HDMI device, such as a camcorder, digital camera or tablet, to an HDMI-enabled device, including computers, Blu-ray™ players, A/V receivers, monitors, projectors and televisions.

Description

Recommended for mobile users who want a cable that can easily pack away in a backpack, laptop bag or camera bag, the one-foot P571-001-MINI High-Speed HDMI to Mini-HDMI Cable (M/M) is designed for use on the go. It connects a camcorder, digital camera, tablet or other device with a mini-HDMI port to an HDMI-enabled device, such as a computer, Blu-ray player, A/V receiver, monitor, projector or television.

The P571-001-MINI supports high-definition video resolutions up to 1920 x 1080 (1080p) at 60 Hz, as well as data transfer speeds up to 10.2 Gbps and HDCP 2.2. It's compliant with HDMI 1.4 standards, including bi-directional Ethernet data transfer, 3D, 4K support and Audio Return Channel.

Foil and braid shielding delivers reliable, error-free signal quality and protection from EMI/RFI line noise that can distort or destroy data. Gold-plated connectors and contacts provide maximum conductivity and minimum data loss. Integral strain relief gives the cable extra flexibility, reduces stress, and helps the cable and connectors move freely without cracking.

Features

Connects Mini-HDMI and HDMI Devices

- Recommended for mobile users who want a cable that can easily pack away in a backpack, laptop bag or camera bag
- Ideal for connecting a mini-HDMI camcorder, digital camera or tablet to an HDMI display

High Performance and Wide Compatibility

Highlights

- Supports HD video resolutions up to 1920 x 1080 (1080p) @ 60 Hz
- Supports data transfer speeds up to 10.2 Gbps
- Compliant with HDMI 1.4 and HDCP 2.2 standards
- Premium foil and braid shielding protects against EMI/RFI noise
- 24K gold-plated connectors for maximum conductivity

Package Includes

- P571-001-MINI High-Speed HDMI to Mini-HDMI Cable (M/M), 1 ft.



- Supports HD video resolutions up to 1920 x 1080 (1080p) @ 60 Hz
- Supports data transfer speeds up to 10.2 Gbps
- Backward compatible with previous HDMI generations
- Complies with HDMI 1.4 and HDCP 2.2

Superior Quality Ensures a Flawless Signal

- 24K gold-plated connectors and contacts for maximum conductivity and minimum data loss
- Integral strain relief protects cable and connectors from stress and cracking
- Foil and braid shielding protects against EMI/RFI line noise that can distort or destroy data
- Flexible PVC jacket easy to install in tight spaces

Specifications

OVERVIEW	
UPC Code	037332205728
INPUT	
Cable Length (ft.)	1
Cable Length (m)	0.3
PHYSICAL	
Color	Black
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Weight (kg)	0.03
Shipping Weight (lbs.)	0.07
Wire Gauge (OD - mm ²)	30
ENVIRONMENTAL	
Operating Temperature Range	14 to 176 F (-10 to 80 C)
Storage Temperature Range	5 to 176 F (-15 to 80 C)
Relative Humidity	0% to 90% RH, Non-Condensing
CONNECTIONS	
Side A - Connector 1	MINI HDMI (MALE)
Side B - Connector 1	HDMI (MALE)
FEATURES & SPECIFICATIONS	



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

HDMI Specification	1.4
HDCP Specification	2.2
Technology	HDMI
STANDARDS & COMPLIANCE	
Certifications	ROHS
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>