

DMS-59 to Dual VGA Splitter Y Cable (M to 2xF), 1 ft. (0.31 m)

MODEL NUMBER: P574-001



Highlights

- Attach two VGA enabled monitors to your DMS59 Graphics card
- Superior molded connectors for long life use

Package Includes

DMS59 to (2) VGA Female Splitter Cable - 1-ft. (0.31 m)

Features

- LFH59 (DMS59) to 2 x VGA Female, 1-ft. (0.31 m)
- Compatible with most DMS-59 video cards including nVidia, Matrox, HP, PNY, and ATI
- Rugged molded construction and gold plated contacts

Specifications

OVERVIEW	
UPC Code	037332145987
Product Type	Passive
Technology	VGA/SVGA
PHYSICAL	
Color	Black
Cable Length (ft.)	1
Cable Length (m)	0.3
Shipping Dimensions (hwd / cm)	27.94 x 17.78 x 1.27
Shipping Dimensions (hwd / in.)	11.00 x 7.00 x 0.50
Shipping Weight (kg)	0.14
Shipping Weight (lbs.)	0.30



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

CONNECTIONS	
Side A - Connector 1	DMS59 (MALE)
Side B - Connector 1	(2) HD15 (FEMALE)
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>