

## DisplayPort Cable with Latching Connectors, 4K 60 Hz (M/M), Black, 3 ft. (0.91 m)

MODEL NUMBER: P580-003



### Highlights

- Digital Video and Audio in one cable
- Supports 1080p resolution
- Small footprint compared to VGA or DVI
- Supports Ultra High Definition (UHD) 4K x 2K video resolutions up to 3840 x 2160 @ 60Hz

### Package Includes

DisplayPort Monitor Cable - 3ft

### Features

- The future standard for Digital Video and Audio connections
- Supports Displayport v1.2
- Supports High Definition Content Protection ( HDCP )
- Supports Ultra High Definition (UHD) 4K x 2K video resolutions up to 3840 x 2160 @ 60Hz, including 1080p

## Specifications

OVERVIEW	
UPC Code	037332160485
Product Type	Passive Cable
Technology	DisplayPort
Cable Type	Passive
VIDEO	
Max Supported Video Resolution	3840 x 2160 (4K) @ 60Hz
Max Supported Color Depth	24-bit True Color
HDR Support	No
3D Video Supported	Yes
Chroma Sub Sampling	4:2:0; 4:2:2
Signal Transmission	Bidirectional



Powering Business Worldwide

TRIPP LITE  
SERIES

CONNECTIONS	
Side A - Connector 1	DISPLAYPORT (MALE)
Side B - Connector 1	DISPLAYPORT (MALE)
Connector Plating	Nickel
Contact Plating	Gold
Connector Style	Straight
Latching or Gripping Connector	Yes
PHYSICAL	
Color	Black
Cable Jacket Color	Black
Cable Jacket Material	PVC
Cable Jacket Rating	VW-1
Cable Outer Diameter (OD)	6.0 mm
Wire Gauge (AWG)	30
Cable Length (ft.)	3
Cable Length (m)	0.91
Cable Length (in.)	36
Ferrite Core	No
Minimum Bend Radius	60mm
Shipping Dimensions (hwd / in.)	9.10 x 7.20 x 0.10
Shipping Dimensions (hwd / cm)	23.11 x 18.29 x 0.25
Shipping Weight (lbs.)	0.14
Shipping Weight (kg)	0.06
ENVIRONMENTAL	
Operating Temperature Range	32° to 113°F (0° to 45°C)
Storage Temperature Range	-40° to 158°F (-40° to 70°C)
Operating Humidity Range	10% to 85% RH, Non-Condensing
Storage Humidity Range	5% to 90% RH, Non-Condensing
COMMUNICATIONS	
EDID Compatible	Yes
Consumer Electronics Control (CEC) Supported	No
FEATURES & SPECIFICATIONS	



Powering Business Worldwide

TRIPP LITE  
SERIES

EMI/RFI Line Noise Protection	No
MST Support	Yes
Antibacterial	No
IP68 Rated	No
Armored Cable	No
Ethernet Support	No
Displayport Specification	1.2
HDCP Specification	2.2
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Compliance	RoHS; REACH; WEEE
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.