

DisplayPort Cable with Latches, 4K @ 30 Hz, (M/M) 30 ft. (9.14 m)

MODEL NUMBER: P580-030



Highlights

- Digital Video and Audio in one cable
- Supports Displayport v1.1
- Supports Ultra High Definition (UHD) 4K x 2K video resolutions up to 3840 x 2160 @ 30Hz, including 1080p
- Small footprint compared to VGA or DVI

Package Includes

DisplayPort Monitor Cable - 30-ft.
(9.14 m)

Features

- The future standard for Digital Video and Audio connections
- Supports Displayport v1.1
- Supports Ultra High Definition (UHD) 4K x 2K video resolutions up to 3840 x 2160 @ 30Hz, including 1080p
- Monitor Resolution Support: 3840 x 2160 @ 30Hz, 2560x1600 @ 60Hz, 1920x1200 @ 120Hz
- Supports High Definition Content Protection (HDCP)
- 28AWG, Aluminum/Mylar Shielding

Specifications

OVERVIEW	
UPC Code	037332185846
Technology	DisplayPort
Cable Type	Passive
VIDEO	
Max Supported Video Resolution	3840 x 2160 @ 30Hz
Max Supported Color Depth	24-bit True Color
Chroma Sub Sampling	4:4:4
PHYSICAL	
Color	Black

Cable Jacket Color	Black
Cable Length (ft.)	30
Cable Length (m)	9.15
Shipping Dimensions (hwd / in.)	12.00 x 10.00 x 0.50
Shipping Dimensions (hwd / cm)	30.48 x 25.40 x 1.27
Shipping Weight (lbs.)	1.06
Shipping Weight (kg)	0.48
CONNECTIONS	
Side A - Connector 1	DISPLAYPORT (MALE)
Side B - Connector 1	DISPLAYPORT (MALE)
Latching or Gripping Connector	Yes
FEATURES & SPECIFICATIONS	
IP68 Rated	No
Displayport Specification	1.1
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; CE (Europe)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty